



Wiring Device-Kellems

Signal and Control, Mini Quick, Female Plug, Field Attachable, Angled, 4-Pole, .16-.24" Cable Range

By Hubbell Wiring Device-Kellems
Catalog # [MCMA14F7](#)



Signal and Control, Mini Quick, Female Plug, Field Attachable, Angled, 4-Pole, .16-.24" Cable Range

Features

- Body with high impact design
- Strain relief protects terminations
- Precision wire funnels eliminate stray strands

Application

Quick Connect/Disconnect Signal and Control

General

EU RoHS Indicator	No
Environmental Conditions	IP67 Ingress Protection
Item Type	Female Angle Plug
Material - Coupling Nut	Aluminum
Material - Insert	PUR/PA
Material - O-Ring	Neoprene
Material - Overmold	PBT
Material - Shell	PBT
OEM Brand Name	Hubbell Wiring Device-Kellems
Operating Temperature	-40 Deg C to 85 Deg C
Performance	<ul style="list-style-type: none"> • Electrical - Amperage - 4A • Electrical - Maximum Wire Size - #18 AWG • Electrical - Voltage Rating - 250V • Environmental - Moisture Resistance - IP66 Suitability • Environmental - Operating Temperature - -40°C to 90°C
Thread Size	Non-Threaded
UPC	783585192437

Electrical Ratings

Amperage Rating	9 A
Current / Amperage Rating	9 A
Current Rating	9 A
Voltage Rating	250V kV

Conductor Related

Cable Size	.16"- .24"
Cable Specification	UL Listed Portable Cord

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • CSA Certified, C22.2 No. 182.3 and CSA C22.2 No. 94.2-07 • UL 2238 and UL50E, File No. E192071
----------------------	---

Logistics

Carton Quantity	30
-----------------	----

Product Assets

- [Literature - WIRING_WLFVM034](#)
- [Literature - Pulp & Paper Solutions](#)
- [Sales Drawings - WDK_MCMA14F7_DRAWING_PDF](#)
- [Warranty - Industrial & Commercial Products](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
WDK-MCMA14F7-SPEC-EN | REV 5/2023

