

Signal and Control Products, Mini-Quick, Female Plug, 4-Pole, Field Attachable, F7

By Hubbell Wiring Device-Kellems
Catalog # [MCMS14F7](#)

Signal and Control Products, Mini-Quick, Female Plug, 4-Pole, Field Attachable, F7

Features

- Body with high impact design
- Strain relief protects terminations
- Precision wire funnels eliminate stray strands

Application

Quick Connect/Disconnect Signal and Control

Performance

- Electrical - Amperage - 4A
- Electrical - Maximum Wire Size - #18 AWG
- Electrical - Voltage Rating - 250V
- Environmental - Moisture Resistance - IP66 Suitability
- Environmental - Operating Temperature - -40°C to 90°C

General

Catalog Number	MCMS14F7
EU RoHS Indicator	No
Environmental Conditions	IP67 Ingress Protection
Item Type	Female Straight Plug
Material - Coupling Nut	Aluminum
Material - Insert	PUR/PA
Material - O-Ring	Neoprene
Material - Overmold	PBT
Material - Shell	PBT
OEM Brand Name	Hubbell Wiring Device-Kellems
Operating Temperature Specifications	-40 Deg C to 85 Deg C <ul style="list-style-type: none">• Connector Insert - Nylon• Connector Shell - PBT• Contacts - Brass, gold plate over palladium nickel• Coupling Nut - Nickel plated brass, SST consult factory



Thread Size	Non-Threaded
UPC	783585192413

Electrical Ratings

Amperage Rating	4 A
Current / Amperage Rating	4 A
Current Rating	4 A
Voltage Rating	250V kV

Conductor Related

Cable Size	.16"- .24"
Cable Specification	UL Listed Portable Cord

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">••• CSA Certified, C22.2 No. 182.3 and CSA C22.2 No. 94.2-07• UL 2238 and UL50E, File No. E192071
----------------------	--

Logistics

Carton Quantity	30
-----------------	----

Product Assets

- [Catalogs - WDK Catalog Full 2024](#)
- [Literature - PULP & PAPER SOLUTIONS](#)
- [Literature - Pulp & Paper Solutions](#)
- [Sales Drawings - WDK_MCMS14F7_DRAWING_PDF](#)
- [Specifications - MCMS14F7](#)
- [Warranty - Industrial & Commercial Products](#)