



Field Attachable Micro-Quick Control Connectors, Female Straight, 4 Wire, Insulation Displacement

By Hubbell Wiring Device-Kellems
Catalog # [MCMS14IDC](#)



Field Attachable Micro-Quick Control Connectors, Female Straight, 4 Wire, Insulation Displacement

Features

- Strain relief bushing protects terminations
- Wire Guide for virtually toolless termination
- Insulation displacement contacts are made of Copper Alloy

Application

Quick Connect/Disconnect Signal and Control

General

| | |
|--------------------|---|
| Color | Black |
| EU RoHS Indicator | Yes |
| Item Type | Female Straight Plug |
| OEM Brand Name | Hubbell Wiring Device-Kellems |
| Performance | <ul style="list-style-type: none">• Electrical - Amperage - 3A• Electrical - Cable Diameters - .160" to .211"• Electrical - Voltage Rating - 32V AC/DC• Electrical - Wire Range - #22 AWG max.• #24 AWG min.• Environmental - Ingress Protection - IP66 Suitability• Environmental - Operating Temperature - -20°C to 110°C |
| Temperature Rating | -20 Deg C to 105 Deg C |
| UPC | 783585226699 |

Dimensions

Diameter Live Part .59"

Conductor Related

Conductor Type Copper
Number Of Conductors 4-Pole

Certifications and Compliance

Industry Standard(s)

- CSA Certified, C22.2 No. 182.3 and CSA C22.2 No. 94.2-07
- UL 2238 and UL50E, File No. E192071

Logistics

Carton Quantity 25

Product Assets

[Literature - WIRING_WLFVM034](#)
[Literature - Pulp & Paper Solutions](#)
[Sales Drawings - WDK_MCMS14IDC_DRAWING_PDF](#)
[Warranty - Industrial & Commercial Products](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
WDK-MCMS14IDC-SPEC-EN | REV 5/2023