



Wiring Device-Kellems

# Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female, Mechanically Interlocked Receptacle, 60A 3-Phase Delta 600V AC,

By Hubbell Wiring Device-Kellems  
 Catalog # [HBL460MI5WR](#)



Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female, Mechanically Interlocked Receptacle, 60A 3-Phase Delta 600V AC, 3-Pole 4-Wire Grounding, Terminal Screws.

## Features

- Captured neoprene gasket for a watertight seal
- DIN rail mounted switch for easy installation and replacement
- Solid pins for longer life and reliable electrical contact

## Application

High Ampacity Watertight Connections

## General

Color	<ul style="list-style-type: none"> <li>• Black</li> <li>• Noir</li> </ul>
Environmental Conditions	Watertight
Item Type	Mechanically Interlocked Single, Reversed
Material	Thermoplastic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3-Pole
Performance	<ul style="list-style-type: none"> <li>• Electrical - Current Interrupting - Certified for current interrupting at full rated current and voltage</li> <li>• Electrical - Dielectric Voltage - Withstands 3,000V AC Min</li> <li>• Electrical - Max. Working Voltage - 600V AC RMS</li> <li>• Environmental - Flammability - UL94-5VA and V-0 Classification</li> <li>• Environmental - Ingress Protection - IP67 Suitability</li> <li>• Environmental - Moisture Resistance - Outdoor - 4X (Watertight, Washdown)</li> <li>• Indoor - 12 (Dust-tight, Falling Dirt and Noncorrosive Liquids).</li> <li>• Environmental - Operating Temperature - Max.</li> </ul>

## Dimensions

Display Size Standard Sized Product

## Electrical Ratings

Amperage Rating	60 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	60 A
Current Rating	60 A
Phase	Three Phase
Voltage Rating	3 Phase 600 VAC
Voltage Rating Description	3 Phase 600 VAC
Wattage	36000

## Conductor Related

Number Of Wires	4-Wire
Wire Size	#8 AWG to #2 AWG

## Certifications and Compliance

Industry Standard(s)	UL Listed
Nema Rating	Non-NEMA

## Product Assets

- [Catalog Page - WDK G-22 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2023](#)
- [Engineering Drawing - HBL460MI5WR AutoCAD Drawing](#)
- [Installation Manuals - WIRING\\_PD1791\\_INSTALLINST](#)
- [Literature - IEC Pin & Sleeve Devices](#)
- [Sales Drawings - WDK\\_HBL460MI\\_DRAWING\\_PDF](#)
- [Warranty - Industrial & Commercial Products](#)

- Temperature -  
Continuous +75°C
- Min. Continuous -40°C
- Mechanical - Impact  
Resistance - In accordance  
with UL 746C
- Mechanical - Mounting -  
External adjustable feet
- Mechanical - Product  
Identification -  
Identification and ratings  
are part of the external  
label and molded into the  
receptacle mount
- Mechanical - Terminal  
Identification - In  
accordance with UL, CSA  
and international  
conventions

Series  
Style  
Type

Non-Fused  
Reverse Service

- Mechanical Interlock
- Mechanical Interlock

UPC

783585012629



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
WDK\_CA-HBL460MI5WR-SPEC-EN | REV 1/2024