

# Field Attachable Micro-Quick Control Connectors, Female Straight, 4 Wire, Insulation Displacement

By Hubbell Wiring Device-Kellems  
Catalog # [MCMS14IDCL](#)



Field Attachable Micro-Quick Control Connectors, Female Straight, 4 Wire, Insulation Displacement

## Features

- Strain relief bushing protects terminations
- Wire Guide for virtually toolless termination
- Insulation displacement contacts are made of Copper Alloy

## General

Application	Quick Connect/Disconnect Signal and Control
Catalog Number	MCMS14IDCL
Color	Black
EU RoHS Indicator	Yes
Item Type	Female Straight Plug
OEM Brand Name	Hubbell Wiring Device-Kellems
Performance	Electrical - Amperage - 6A  Electrical - Cable Diameters - .22" to .32"  Electrical - Voltage Rating - 50V AC/DC  Electrical - Wire Range - #18 AWG max., #22 AWG min.  Environmental - Ingress Protection - IP66 Suitability  Environmental - Operating Temperature - -20°C to 110°C
Temperature Rating	-20 Deg C to 105 Deg C
UPC	783585226774

## Dimensions

Diameter Live Part	.59"
--------------------	------

## Conductor Related

Conductor Type	Copper
Number of Conductors	4-Pole

## Certifications And Compliance

Industry Standard(s)	CSA Certified, C22.2 No. 182.3 and CSA C22.2 No. 94.2-07  UL 2238 and UL50E, File No. E192071
----------------------	---

## Logistics

Carton Quantity	25
-----------------	----

## Product Assets

[Catalogs - WDK Catalog Full 2024](#)  
[Installation Manuals - WIRING\\_PD1939\\_INSTALLINST](#)  
[Literature - Pulp & Paper Solutions](#)  
[Literature - PULP & PAPER SOLUTIONS](#)  
[Sales Drawings - WDK\\_MCMS14IDCL\\_DRAWING\\_PDF](#)  
[Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
WDK-MCMS14IDCL-SPEC-EN | REV 6/2024