



Micro-Quick Control Connectors, Male Angled, 3 Wire, Insulation Displacement

By Hubbell Wiring Device-Kellems
Catalog # [MIMA13IDC](#)



Micro-Quick Control Connectors, Male Angled, 3 Wire,
Insulation Displacement

Features

- Strain relief bushing protects terminations
- Wire Guide for virtually toolless termination
- Insulation displacement contacts are made of Copper Alloy

Application

Quick Connect/Disconnect Signal and Control

General

Color	Black
EU RoHS Indicator	Yes
Item Type	Male Angled In-Line Plug
OEM Brand Name	Hubbell Wiring Device-Kellems
Performance	<ul style="list-style-type: none"> • Electrical - Amperage - 3A • Electrical - Cable Diameters - .160" to .211" • Electrical - Voltage Rating - 32V AC/DC • Electrical - Wire Range - #22 AWG max. • #24 AWG min. • Environmental - Ingress Protection - IP66 Suitability • Environmental - Operating Temperature - -20°C to 110°C
Temperature Rating	-20 Deg C to 105 Deg C
UPC	783585226705

Dimensions

Diameter Live Part .67"

Conductor Related

Conductor Type Copper
Number Of Conductors 3-Pole

Certifications and Compliance

Industry Standard(s)

- CSA Certified, C22.2 No. 182.3 and CSA C22.2 No. 94.2-07
- UL 2238 and UL50E, File No. E192071

Logistics

Carton Quantity 25

Product Assets

[Literature - WIRING_WLFVM034](#)
[Literature - Pulp & Paper Solutions](#)
[Sales Drawings - WDK_MIMA13IDC_DRAWING_PDF](#)
[Warranty - Industrial & Commercial Products](#)



A proud member of the Hubbell Family.