



Locking Devices, Twist-Lock®, Industrial, Panel Mount Receptacle, 15A 125V, 2-Pole 3-Wire Grounding, L5-15R, Screw Terminal, Mounted to 4" Box Cover

By Hubbell Wiring Device-Kellems
Catalog # [HBL4711](#)



Twist-Lock® Single Receptacle, 15A, 125V, 2-Pole, 3 Wire Grounding, NEMA L5-15R, Mounted on a 4" Round Box Cover.

Features

- Reinforced thermoplastic construction
- Single piece, all brass contacts
- All terminals are back and side wired
- Brass mounting strap with stainless steel grounding clip

Application

Heavy Duty Industrial

General

Color	Black
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	0.5
Item Type	15A Single Receptacle Mounted to 4" Round Box Cover
Listings	<ul style="list-style-type: none"> • UL 498 • Fed.Spec. W-C-596 • CSA C22.2 No.42
Material	Nylon
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	<ul style="list-style-type: none"> • Electrical-Current Interrupting - Certified for current interrupting at full rated current • Electrical - Dielectric Voltage - Withstands 2,000V minimum • Mechanical - Terminal Accommodation - #18 - #10 AWG stranded copper wire only • Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 • Environmental

Dimensions

Dimensions	1.42 in x 1.42 in x 1.27 in
Display Size	Standard Sized Product
Height	1.27 in
Length	1.42 in
Weight	0.25 lb
Width	1.42 in

Electrical Ratings

Amperage Rating	15 A
Connectivity	Screw Terminals
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 VAC

Conductor Related

Number Of Wires	3-Wire Grounding
Wire Size	#18 AWG to #10 AWG

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • Certified to CSA C22.2 No.42 • Fed. Spec. W-C-596 • Listed to UL 498
----------------------	--

Nema Rating	L5-15R
-------------	--------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [BIM - Specialty_Equipment-Metal_Raceway-Hubbell_Wiring-Flat_Elbow_Undivided-HBL4711](#)
- [Catalog Page - WDK B-13 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2023](#)
- [Sales Drawings - WDK_HBL4711_DRAWING_PDF](#)
- [Warranty - Industrial & Commercial Products](#)
- [Video - Insulgrip Twist-Lock and Straight Blade Devices](#)
- [Video - Twist-Lock Devices](#)

Related Products

- Environmental -
Flammability - HB or better
per UL94/CSA 22.2 No.0.17
- Environmental - Operating
Temperatures - Maximum
Continuous 75°C
- Minimum -40°C (w/o
impact)

UPC

783585236742

Related Products

SS7L - Wallplates and Boxes, Metallic Plates, 1- Gang, 1) 1.40" Opening, 430 Stainless Steel

SS7 - Wallplates and Boxes, Metallic Plates, 1- Gang, 1) 1.40" Opening, Standard Size, Stainless Steel

HBL4720C - Locking Devices, Twist-Lock®, Industrial, Male Plug, 15A 125V, 2-Pole 3-Wire Grounding, L5-15P, Screw Terminal, Black and White

HBL7420 - Wallplates and Boxes, Weatherproof Covers, 1- Gang, 1) 1.40" to 1.60" Opening, Standard Size, Aluminum

HBL4720CBK - Locking Devices, Twist-Lock®, Industrial, Male Plug, 15A 125V, 2-Pole 3-Wire Grounding, L5-15P, Screw Terminal, Black



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WDK_CA-HBL4711-SPEC-EN | REV 1/2024