



# Locking Devices, Twist-Lock®, Industrial, Male Plug, 15A 125V, 2-Pole 3-Wire Grounding, L5-15P, Screw Terminal, Black and White

By Hubbell Wiring Device-Kellems  
Catalog # [HBL4720C](#)



Twist-Lock® Insulgrip® Male Plug, 15A 125V, 2-Pole, 3-Wire Grounding, NEMA L5-15P/White Nylon.

## Features

- Individually molded face for each blade configuration
- Roomy wiring chamber provides ample space for wiring
- Ribbed nylon housing provides a secure grip that's impact and chemical resistant

## Application

Extra Heavy Duty Industrial

## General

Color	Noir, blanc
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	0.5
Item Type	15A Grounding Insulgrip® Plug
Material	Nylon
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	<ul style="list-style-type: none"> <li>• Electrical - Current Interrupting - Certified for current interrupting at full rated current</li> <li>• Electrical - Dielectric Voltage - Withstands 2,000V minimum</li> <li>• Environmental - Flammability - HB or better per UL94 or CSA 22.2 No. 0.6</li> <li>• Environmental - Moisture Resistance - IP20 Suitability</li> <li>• Environmental - Operating Temperatures - Maximum Continuous 75°C Minimum -40°C (w/o impact)</li> <li>• Mechanical - Terminal Accommodation - #16 AWG - #8 AWG stranded copper wire only.</li> <li>• Mechanical - Terminal Identification - Terminals</li> </ul>

## Dimensions

Dimensions	1.53 in x 1.53 in x 1.97 in
Display Size	Standard Sized
Height	1.97 in
Length	1.53 in
Weight	0.15 lb
Width	1.53 in

## Electrical Ratings

Amperage Rating	15 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V

## Conductor Related

Cable Range	0.230 - 0.720 in
Cord Type	All Listed Portables
Number Of Wires	3-Wire
Wire Size	#16 AWG to #8 AWG

## Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> <li>• Certified to CSA C22.2 No.42</li> <li>• Fed.Spec. W-C-596</li> <li>• Listed to UL 498</li> </ul>
Nema Rating	L5-15P
Standards - RoHS Compliance Status	CM

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalog Page - WDK B-12 Catalog Page](#)  
[Catalogs - WDK Catalog Full 2023](#)  
[Engineering Drawing - HBL4720C AutoCAD Drawing](#)  
[Installation Manuals - WIRING\\_PD2437\\_INSTALLINST](#)  
[Literature - Food Processing Guide](#)  
[Literature - Insulgrip® Straight Blade and Twist-Lock® Devices](#)

identification - terminals  
identified in accordance  
with UL 498

[Literature - Healthcare Application Guide](#)  
[Literature - Industrial Solutions](#)  
[Literature - Education Application Guide](#)  
[Literature - Emergency Preparedness for Healthcare](#)  
[Literature - Entertainment Product Solution Guide](#)  
[Sales Drawings - WDK\\_HBL4720C\\_DRAWING\\_PDF](#)  
[Warranty - Industrial & Commercial Products](#)  
[Video - Insulgrip Twist-Lock and Straight Blade Devices](#)  
[Video - Twist-Lock Devices](#)

Type

- Plugs
- Plugs

UPC

783585171159



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
WDK\_CA-HBL4720C-SPEC-EN | REV 1/2024