



# Straight Blade Devices, Receptacles, Duplex, Industrial Grade, 2-Pole 3-Wire Grounding, 15A 125V, 5-15R, Brown, Single Pack

By Hubbell Wiring Device-Kellems  
Catalog # [HBL5262](#)



HBL® Straight Blade Extra Heavy Duty MAX Duplex Receptacle  
15A, 2-Pole, 3-Wire Grounding, 125V, 5-15R, Back and Side  
Wired.

## Features

- Back wired ground terminal allows faster, easier installation
- One-piece brass integral ground strap
- Finder Groove Face
- Deep body design with circuit ID face

## Application

Extra Heavy Duty Specification Grade

## General

Color	<ul style="list-style-type: none"> <li>• Brun</li> <li>• Marron</li> </ul>
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	0.5
Item Type	Traditional Duplex
Material	Nylon
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	<ul style="list-style-type: none"> <li>• Electrical - Current Interrupting - Certified for current interrupting at full rated current</li> <li>• Electrical - Dielectric Voltage - Withstands 2,000V minimum</li> <li>• Environmental - Flammability - Top: UL 94V-2, Base: UL 94V-0</li> <li>• Environmental - Operating Temperatures - Maximum continuous 75°C, minimum -40°C (w/o impact)</li> <li>• Mechanical - Product Identification - Ratings are a permanent part of the device</li> <li>• Mechanical - Terminal</li> </ul>

## Dimensions

Dimensions	3.28 in x 1.65 in x 1.19 in
Display Size	Standard Sized Product
Height	1.19 in
Length	3.28 in
Weight	0.25 lb
Width	1.65 in

## Electrical Ratings

Amperage Rating	15 A
Connectivity	Back and Side Wired
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 VAC
Voltage Rating Description	125 V
Wattage	1875 W

## Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #10 AWG

## Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> <li>• Certified to CSA 22.2, No. 42 File 285</li> <li>• Fed. Spec. W-C-596</li> <li>• NEMA® WD-6 Compliant</li> <li>• UL Listed to UL498 File No. E2186</li> </ul>
----------------------	-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

Nema Rating	5-15R
Standards - RoHS Compliance Status	CM

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalog Page - WDK A-10](#) [Catalog Page - WDK A-56](#)

Accommodation - #14-#10  
AWG copper stranded or  
solid conductor only

- Mechanical - Terminal  
Identification - Terminals  
identified in accordance  
with UL 498 and CSA

[Catalog Page - WDK O-33 Catalog Page](#)  
[Catalogs - WDK Catalog Full 2023](#)  
[Engineering Drawing - HBL5262 AutoCAD Drawing](#)  
[Installation Manuals - WIRING\\_PD2615\\_INSTALLINST](#)  
[Literature - Industrial Solutions](#)  
[Literature - Education Application Guide](#)  
[Literature - Wiring Device Solutions for Strategic  
Manufacturing Facilities](#)  
[Sales Drawings - WDK\\_HBL5262\\_DRAWINGS\\_PDF](#)  
[Warranty - Industrial & Commercial Products](#)

Series  
Style  
Type  
  
UPC

Extra Heavy Duty  
Finder Groove Face

- Standard Duplex
- Standard Duplex

783585435107



**A proud member of the Hubbell Family.**

©2024 Hubbell Incorporated. All rights reserved.  
WDK\_CA-HBL5262-SPEC-EN | REV 1/2024