

**HUBBELL**  
Wiring Device-Kellems

**Straight Blade Devices, Male Plug,  
Insulgrip Heavy Duty,  
Industrial/Commercial Grade,  
Straight, 2-Pole 3- Wire Grounding,  
15A125V, 5-15P, Single Pack**

By Hubbell Wiring Device-Kellems  
Catalog # [HBL5266CM2](#)

Straight Blade Male Plug, Insulgrip Heavy Duty,  
Industrial/Commercial Grade, Straight, 2-Pole 3-Wire Grounding,  
15A125V, 5-15P.



## General

Catalog Number	HBL5266CM2
Color	
Material	Polycarbonate
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	Electrical - Current Interrupting - Certified for current interrupting at full rated current  Electrical - Dielectric Voltage - Withstands 2,000V minimum  Environmental - Flammability - UL 94 HB or better  Environmental - IP Suitability - IP20  Environmental - Operating Temperatures - Maximum continuous 75°C minimum -40°C (w/o impact)  Mechanical - Terminal Accommodation - #18-10 AWG. Standed copper wire only  Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA
Series	Insulgrip®
Style	Standard
Type	
UPC	783585848501

## Dimensions

Dimensions	1.52 in x 1.52 in x 1.96 in
Height	1.96 in
Length	1.52 in
Weight	0.15 lb
Width	1.52 in

## Electrical Ratings

Amperage Rating	15 A
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Voltage Rating	125 VAC
Voltage Rating Description	125 V

## Conductor Related

Number Of Wires	3-Wire
Wire Size	#18 AWG to #10 AWG

## Certifications And Compliance

Industry Standard(s)	CSA Certified to C22.2 No. 42 File 280 Fed. Spec. W-C596G NEMA® WD-6 Compliant UL Listed to UL498 File E1706
Nema Rating	5-15P
Standards - RoHS Compliance Status	CM

## Logistics

Carton Quantity	10
Pallet Quantity	4500

## Product Assets

[Catalogs - WDK Catalog Full 2024](#)  
[Engineering Drawing - HBL5266C AutoCAD Drawing](#)  
[Engineering Drawing - HBL5266CM2 AutoCAD Drawing](#)  
[Installation Manuals - WIRING\\_PD2437\\_INSTALLINST](#)  
[Installation Manuals - WIRING\\_PD1214\\_INSTALLINST](#)  
[Literature - Insulgrip® Straight Blade and Twist-Lock® Devices](#)  
[Literature - Industrial Solutions](#)  
[Literature - Entertainment Product Solution Guide](#)  
[Product Cross Section Image\(s\) - WBP\\_HBL5266C\\_LINEDIAGRAM\\_PRODIMAGE](#)  
[Sales Drawings - WDK\\_HBL5266\\_DRAWING\\_PDF](#)  
[Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
WDK\_CA-HBL5266CM2-SPEC-EN | REV 6/2024