



Straight Blade Devices, Receptacles, Duplex, Commercial Grade, 2-Pole 3-Wire Grounding, 15A 277V AC, 7-15R, Brown, Single Pack

By Hubbell Wiring Device-Kellems
Catalog # [HBL5302](#)



Straight Blade Flush Duplex Receptacle 15A, 2-Pole, 3-Wire
Grounding, 15A 277V, 7-15R.

Features

- Finder groove face
- Auto ground clip

Application

Heavy Duty

General

Color	<ul style="list-style-type: none"> • Brown • Brun
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	2
Item Type	Single
Material	Thermoplastic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	<ul style="list-style-type: none"> • Electrical - Current Interrupting - Certified for current interrupting at full rated current • Electrical - Dielectric Voltage - Withstands 2,000V minimum • Environmental - Flammability - UL 94 V-0 • Environmental - Operating Temperatures - Maximum continuous 75°C minimum -40°C (w/o impact) • Mechanical - Product Identification - Ratings are a permanent part of the device • Mechanical - Terminal Accommodation - #14-#10 AWG copper stranded or solid conductor only • Mechanical - Terminal

Dimensions

Dimensions	3.28 in x 1.33 in x 1.19 in
Display Size	Standard Sized Product
Height	1.19 in
Length	3.28 in
Weight	0.25 lb
Width	1.33 in

Electrical Ratings

Amperage Rating	15 A
Connectivity	Back and Side Wired
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	277 VAC
Voltage Rating Description	277 V
Wattage	4155 W

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #10 AWG

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • CSA Certified to C22.2 No. 42 File 280C • NEMA® WD-6 Compliant • UL Listed to UL498 File E1706
Nema Rating	7-15R
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - WDK A-41 Catalog Page](#)
[Catalog Page - WDK O-33 Catalog Page](#)
[Catalogs - WDK Catalog Full 2023](#)
[Installation Manuals - WIRING_PD2615_INSTALLINST](#)

Identification - Terminals
identified in accordance
with UL 498 and CSA

Literature - WIRING_WLFVM034
Literature - Pulp & Paper Solutions
Sales Drawings - WDK_HBL5302_DRAWING_PDF
Warranty - Industrial & Commercial Products

Series

Extra Heavy Duty

Type

- Standard Duplex
- Standard Duplex

UPC

783585014241



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WDK_CA-HBL5302-SPEC-EN | REV 1/2024