



Kellems Wire Management, Pulling Grips, Splicing Grip, .75"-.99", Galvanized, 24" Long

By Hubbell Wiring Device-Kellems
Catalog # [01304010](#)

Kellems® Cable Splicing Grip, .75"-.99", Galvanized, 24" Long.



Features

- Double weave construction
- Suitable for splicing

Application

Cable and Wire Splicing

General

| | |
|------------------------------|--|
| Approx Breaking Strength | 7,500 lbs |
| Color | <ul style="list-style-type: none">• Metallic• Métallique |
| Environmental Conditions | No Limitations |
| Material | Steel, Galvanized |
| Material - Mounting Hardware | On Cable Ends |
| Performance | <ul style="list-style-type: none">• Mechanical - Approximate Breaking Strength - 7,500 (33,360) Lbs. (N)• Mechanical - Cable Diameter Range - .75"-.99" (1.90-2.51)• Mechanical - Working Load - (program formula 5% of Approximate Breaking Strength) |
| Series | Splicing Grips |
| Style | Closed Mesh, Double Weave |
| Type | <ul style="list-style-type: none">• Tube• Tube |
| UPC | 783585300078 |

Dimensions

Display Size 24" (60.96) Length

Conductor Related

Cable Diameter Range 0.75 in-0.99 in
Cable Size .75"-.99" (1.90-2.51)
Number Of Conductors 1 Jacketed Cable

Certifications and Compliance

Industry Standard(s) CSA Certified

Product Assets

- [Catalog Page - WDK W-15 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2023](#)
- [Literature - WIRING_WLFVM034](#)
- [Literature - Wire Management Solutions Brochure](#)
- [Literature - Wiring_WLFVM032](#)
- [Literature - Wiring_WLBVM044](#)
- [Literature - Pulp & Paper Solutions](#)
- [Sales Drawings - WDK_01304010_DRAWING_PDF](#)
- [Warranty - Industrial & Commercial Products](#)
- [Video - Kellems Wire Management Solutions](#)
- [Video - Kellems Wire Management Solutions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WDK_CA-01304010-SPEC-EN | REV 1/2024