



Wiring Device-Kellems

Kellems Wire Management, Pulling Grips, Splicing Grip, .62"-.74", Galvanized, 24" Long

By Hubbell Wiring Device-Kellems
Catalog # [01304013](#)

Kellems® Cable Splicing Grip, .62"-.74", Galvanized, 24" Long.



Features

- Double weave construction
- Suitable for splicing

Application

Cable and Wire Splicing

General

Approx Breaking Strength	4,400 lbs
Color	<ul style="list-style-type: none"> • Metallic • Métallique
Environmental Conditions	No Limitations
Material	Steel, Galvanized
Material - Mounting Hardware	On Cable Ends
Performance	<ul style="list-style-type: none"> • Mechanical - Approximate Breaking Strength - 4,400 (19,571) Lbs. (N) • Mechanical - Cable Diameter Range - .62"-.74" (1.57-1.88) • Mechanical - Working Load - (program formula 5% of Approximate Breaking Strength)
Series	Splicing Grips
Style	Closed Mesh, Double Weave
Type	<ul style="list-style-type: none"> • Tube • Tube
UPC	783585326986

Dimensions

Display Size 24" (60.96) Length

Conductor Related

Cable Diameter Range 0.62 in-0.74 in
 Cable Size .62"-.74" (1.57-1.88)
 Number Of Conductors 1 Jacketed Cable

Certifications and Compliance

Industry Standard(s) CSA Certified

Product Assets

- [Catalog Page - WDK W-15 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2023](#)
- [Literature - WIRING_WLFVM034](#)
- [Literature - Wire Management Solutions Brochure](#)
- [Literature - Wiring_WLFVM032](#)
- [Literature - Wiring_WLBVM044](#)
- [Literature - Pulp & Paper Solutions](#)
- [Sales Drawings - WDK_01304013_DRAWING_PDF](#)
- [Warranty - Industrial & Commercial Products](#)
- [Video - Kellems Wire Management Solutions](#)
- [Video - Kellems Wire Management Solutions](#)



A proud member of the Hubbell Family.