



Wiring Device-Kellems

# Kellems Wire Management, Pulling Grips, Splicing Grip, 1.00"-1.49", Galvanized, 36" Long

By Hubbell Wiring Device-Kellems  
Catalog # [01304055](#)

Kellems® Cable Splicing Grip, 1"-1.49", Galvanized, 36" Long.



## Features

- Double weave construction
- Suitable for splicing

## Application

Cable and Wire Splicing

## General

Approx Breaking Strength	10,000 lbs
Color	<ul style="list-style-type: none"> <li>• Metallic</li> <li>• Métallique</li> </ul>
Environmental Conditions	No Limitations
Material	Steel, Galvanized
Material - Mounting Hardware	On Cable Ends
Performance	<ul style="list-style-type: none"> <li>• Mechanical - Approximate Breaking Strength - 10,000 (44,480) Lbs. (N)</li> <li>• Mechanical - Cable Diameter Range - 1.00"-1.49" (2.54-3.78)</li> <li>• Mechanical - Working Load - (program formula 5% of Approximate Breaking Strength)</li> </ul>
Series	Splicing Grips
Style	Closed Mesh, Double Weave
Type	<ul style="list-style-type: none"> <li>• Tube</li> <li>• Tube</li> </ul>
UPC	783585300245

## Dimensions

Display Size 36" (91.44) Length

## Conductor Related

Cable Diameter Range 1.00 in-1.49 in  
 Cable Size 1.00"-1.49" (2.54-3.78)  
 Number Of Conductors 1 Jacketed Cable

## Certifications and Compliance

Industry Standard(s) CSA Certified

## Product Assets

- [Catalog Page - WDK W-15 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2023](#)
- [Literature - WIRING\\_WLFVM034](#)
- [Literature - Wire Management Solutions Brochure](#)
- [Literature - Pulp & Paper Solutions](#)
- [Sales Drawings - WDK\\_01304055\\_DRAWING\\_PDF](#)
- [Warranty - Industrial & Commercial Products](#)
- [Video - Kellems Wire Management Solutions](#)
- [Video - Kellems Wire Management Solutions](#)



A proud member of the Hubbell Family.