

Straight Blade Devices, Decorator
Duplex Receptacle, Hospital Grade,
Hubbell-Pro, LED Indicator, 20A
125V, 2- Pole3-Wire Grounding, 5-
20R, Ivory

By Hubbell Wiring Device-Kellems
Catalog # 2182IVL

Straight Blade Devices, Decorator Duplex Receptacle, Hospital
Grade, Hubbell-Pro, LED Indicator, 20A 125V, 2- Pole3-Wire
Grounding, 5-20R, Ivory.

Features

- Green LED Power Indicators to identify emergency circuits
- Triple wipe contacts
- High impact resistant decorator face
- Steel mounting strap

Application

Hubbell-Pro Heavy Duty Hospital Grade

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - UL 94V-2
- Environmental - Operating Temperature - Maximum continuous 75°C, minimum -40°C (w/o impact)
- Mechanical - Product Identification - Ratings are a permanent part of the device
- Mechanical - Terminal Accommodation - #12-#10 AWG stranded or solid copper wire only
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

General

Catalog Number	2182IVL
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	1
Indicator(s) Type	Green LED
Item Type	Style Line Decorator Duplex
Material	Nylon
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Series	Hubbell-Pro



Specifications

- Automatic Self-grounding Staple - Stainless steel
- Base - PBT
- Clamping Plate - Plated steel
- Face - Nylon
- Ground Contacts - Brass
- Mounting Screws - Zinc plated steel
- Mounting Strap - Galvanized steel
- Power Contacts - Brass

Style
Type
UPC

Style Line decorator
Duplex Receptacle
783585196145

Dimensions

Dimensions	3.28 in x 1.57 in x 1.15 in
Display Size	Standard Sized Product
Height	1.15 in
Length	3.28 in
Weight	0.15 lb
Width	1.57 in

Electrical Ratings

Amperage Rating	20 A
Connectivity	Back and Side Wired Screw Terminals
Current / Amperage Rating	20 A
Current Rating	20 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 VAC
Voltage Rating Description	125 V
Wattage	2500 W

Conductor Related

Number Of Wires	3-Wire
-----------------	--------

Wire Size

#12 AWG to #10 AWG

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">Certified to CSA, C22.2, No. 42 File 285Fed. Spec. W-C-596NEMA® WD-6 CompliantUL Listed to UL498 File No. E2186
Nema Rating	5-20R

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- Catalog Page - WDK L-9 Catalog Page
- Catalog Page - WDK A-27 Catalog Page
- Catalogs - WDK Catalog Full 2024
- Engineering Drawing - 2182IVL AutoCAD Drawing
- Installation Manuals - WIRING_PD2504_INSTALLINST
- Literature - Duct Products Guide
- Literature - Hubbell-Pro Hospital Grade Receptacles
- Sales Drawings - WDK_2182L_DRAWINGS_PDF
- Specifications - 2182IVL Specification Sheet French
- Specifications - 2182IVL Specification Sheet
- Specifications - Wiring 2182IVL Specification Sheet
- Warranty - Industrial & Commercial Products