

Straight Blade Devices,
Receptacles, Duplex,
Commercial/Industrial Grade, 2-
Pole 3-Wire Grounding, 15A 125V, 5-
15R, White

By Hubbell Wiring Device-Kellems
Catalog # [5262W](#)



Straight Blade Devices, Receptacles, Duplex,
Commercial/Industrial Grade, 2-Pole 3-Wire Grounding, 15A
125V, 5-15R, White

Features

- Slender/compact design
- Finder Groove Face
- Triple wipe contacts

Application

Hubbell-Pro Extra Heavy Duty

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - UL 94 V-2
- Environmental - Operating Temperatures - Maximum continuous 75°C, minimum -40°C (w/o impact)
- Mechanical - Product Identification - Ratings are a permanent part of the device
- Mechanical - Terminal Accommodation - #14-#10 AWG copper stranded or solid conductor only
- Mechanical - Terminal Identification - Terminal wire leads identified in accordance with UL 498

General

Catalog Number	5262W
Color	White
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry unless protected by additional means
Horsepower - Maximum	0.5
Item Type	Traditional Duplex
Material	Thermoplastic/Composite
Material - Mounting Hardware	Screw Mounting
Mounting Type	Screw Mount
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Series	Hubbell-PRO

Size
Specifications

- Standard Sized Product
- Automatic Self-grounding Staple - Stainless steel
 - Base - PBT
 - Contacts - Brass
 - Face - Nylon
 - Mounting Screws - Zinc plated steel
 - Mounting Strap - Galvanized steel
- Finder Groove Face
Maximum continuous 75°C;
minimum -40°C (w/o impact)
Standard Duplex
783585834979

Style
Temperature Rating

Type
UPC

Dimensions

Dimensions	3.28 in x 1.41 in x 1.09 in
Display Size	Standard Sized Product
Height	1.09 in
Length	3.28 in
Weight	0.2 lb
Width	1.41 in

Electrical Ratings

Amperage Rating	15 A
Connectivity	Back and Side Wired
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	1875 W

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #10 AWG

Certifications And Compliance

Industry Standard(s)	UL File No. E2186, Certified to CSA 22.2, No. 42 File 285, Fed. Spec. W-C-596, NEMA® WD-6 Compliant
Nema Rating	5-15R

Logistics

Carton Quantity	10
Pallet Quantity	5500

Product Assets

- Catalog Page - WDK A-28 Catalog Page
- Catalogs - WDK Catalog Full 2024
- Engineering Drawing - M10822_ACAD
- Installation Manuals - WIRING_PD2504_INSTALLINST
- Sales Drawings - M10822
- Specifications - 5262W Specification Sheet
- Specifications - 5262W Specification Sheet French
- Specifications - Wiring 5262W Specification Sheet
- Warranty - Industrial & Commercial Products



A Hubbell brand