




Straight Blade Devices, Receptacles, Duplex, Industrial Grade, 2-Pole 3-Wire Grounding, 20A 125V, 5-20R, Brown, Single Pack

By Hubbell Wiring Device-Kellems
Catalog # [HBL5362](#)



HBL® Extra Heavy Duty MAX Straight Blade Duplex Receptacle
20A, 2-Pole, 3-Wire Grounding, 125V, 5-20R.

Features

- Back wired ground terminal allows faster, easier installation
- One-piece brass integral ground strap
- Finder Groove Face
- Deep body design with circuit ID face

Application

Extra Heavy Duty Specification Grade

General

| | |
|------------------------------|---|
| Color | <ul style="list-style-type: none"> • Brown • Marron |
| Environmental Conditions | Indoor Dry Unless Protected By Additional Means |
| Horsepower - Maximum | 1 |
| Item Type | Traditional Duplex |
| Material - Mounting Hardware | Screw Mounting |
| Number Of Poles | 2-Pole |
| Operating Temperature | Maximum continuous 75°C and minimum -40°C without Impact |
| Performance | <ul style="list-style-type: none"> • Electrical - Current Interrupting - Certified for current interrupting at full rated current • Electrical - Dielectric Voltage - Withstands 2,000V minimum • Environmental - Flammability - Top: UL 94V-2, Base: UL 94V-0 • Environmental - Operating Temperatures - Maximum continuous 75°C, minimum -40°C (w/o impact) • Mechanical - Product Identification - Ratings are a permanent part of the device • Mechanical - Terminal Accommodation - #14-#10 AWG copper stranded or |

Dimensions

| | |
|--------------|-----------------------------|
| Dimensions | 3.28 in x 1.65 in x 1.19 in |
| Display Size | Standard Sized Product |
| Height | 1.19 in |
| Length | 3.28 in |
| Weight | 0.25 lb |
| Width | 1.65 in |

Electrical Ratings

| | |
|----------------------------|-------------------------------------|
| Amperage Rating | 20 A |
| Connectivity | Back and Side Wired Screw Terminals |
| Current / Amperage Rating | 20 A |
| Current Rating | 20 A |
| Dielectric Strength | Withstands 2,000V minimum |
| Phase | Single Phase |
| Voltage Rating | 125 VAC |
| Voltage Rating Description | 125 V |
| Wattage | 2500 W |

Conductor Related

| | |
|-----------------|--------------------|
| Number Of Wires | 3-Wire |
| Wire Size | #14 AWG to #10 AWG |

Certifications and Compliance

| | |
|------------------------------------|---|
| Industry Standard(s) | <ul style="list-style-type: none"> • Certified to CSA 22.2, No. 42 File 285 • Fed. Spec. W-C-596 • NEMA® WD-6 Compliant • UL Listed to UL498 File No. E2186 |
| Nema Rating | 5-20R |
| Standards - RoHS Compliance Status | CM |

Logistics

| | |
|-----------------|----|
| Carton Quantity | 10 |
|-----------------|----|

Product Assets

[Catalog Page - WDK A-10 Catalog Page](#)
[Catalog Page - WDK Q-33 Catalog Page](#)

| | | |
|--------|---|---|
| | solid conductor only | Catalogs - WDK Catalog Full 2023 |
| | <ul style="list-style-type: none"> Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA | Engineering Drawing - HBL5362 AutoCAD Drawing Installation Manuals - WIRING_PD2615_INSTALLINST Literature - Wiring Device Solutions for Strategic Manufacturing Facilities Literature - Industrial Solutions Literature - Education Application Guide Sales Drawings - WDK_HBL5362_DRAWINGS_PDF Warranty - Industrial & Commercial Products |
| Series | Extra Heavy Duty | |
| Style | Finder Groove Face | |
| Type | <ul style="list-style-type: none"> Standard Duplex Standard Duplex | |
| UPC | 783585435220 | |



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WDK_CA-HBL5362-SPEC-EN | REV 1/2024