



Straight Blade Devices, Tamper Resistant Duplex Receptacle, Industrial Grade, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, White

By Hubbell Wiring Device-Kellems
Catalog # [HBL5362WTR](#)



Straight Blade Devices, Tamper Resistant Duplex Receptacle, Industrial Grade, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, White.

Features

- Patented TR design eliminates plug-in difficulty and TR complaints
- Fed-Spec UL listing insures proven performance in demanding applications
- Brass mounting strap and Triple Wipe contacts
- High impact resistant face with circuit I.D. marking area
- Complies with National Electrical Code (NEC®) requirements for Tamper Resistant receptacles

Application

Extra Heavy Duty Specification Grade

General

Color	<ul style="list-style-type: none"> • White • Blanc
Horsepower - Maximum	1
Item Type	Traditional Duplex
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	<ul style="list-style-type: none"> • Electrical - Current Interrupting - Certified for current interrupting at full rated current • Electrical - Dielectric Voltage - Withstands 2,000V minimum • Environmental - Flammability - UL 94 V-2 • Environmental - Operating Temperatures - Maximum continuous 75°C, minimum -40°C (w/o impact) • Mechanical - Product Identification - Ratings are a permanent part of the device • Mechanical - Terminal Accommodation - #12-#10 AWG stranded or solid

Dimensions

Display Size	Standard Sized Product
Length	3.28 in
Weight	0.2 lb
Width	1.32 in

Electrical Ratings

Amperage Rating	20 A
Connectivity	Back and Side Wired Screw Terminals
Current / Amperage Rating	20 A
Current Rating	20 A
Dielectric Strength	Withstands 2,000V minimum
Voltage Rating	125 VAC
Voltage Rating Description	125 V
Wattage	2500 W

Conductor Related

Number Of Wires	3-Wire
Wire Size	#12 AWG to #10 AWG

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • CSA Certified 22.2, No. 42 • Fed. Spec. W-C-596 • NEMA® WD-6 Compliant • UL Listed to UL498 File No. E2186
----------------------	---

Nema Rating	5-20R
-------------	-------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - WDK A-11 Catalog Page](#)
[Catalogs - WDK Catalog Full 2023](#)
[Engineering Drawing - HBL5362WTR AutoCAD Drawing](#)
[Installation Manuals - WIRING_PD1579_INSTALLINST](#)
[Literature - Heavy Duty Tamper-Resistant Receptacles](#)
[Literature - Tamper-Resistant Receptacles](#)
[Sales Drawings - WDK_HBL5362TR_DRAWINGS_PDF](#)
[Warranty - Industrial & Commercial Products](#)
[Video - Tamper-Resistant Receptacles](#)

- AWC stranded or solid copper wire only
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

Series

Extra Heavy Duty

Style

Smooth Face

Type

- Tamper-Resistant
- Tamper-Resistant

UPC

783585542546



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WDK_CA-HBL5362WTR-SPEC-EN | REV 1/2024