

Straight Blade Devices, Tamper
Resistant Duplex Receptacle,
Hubbell-Pro, Hospital Grade, 2-Pole
3-Wire Grounding, 15A 125V, 5-15R,
Black

By Hubbell Wiring Device-Kellems
Catalog # [8200BKTRA](#)

Straight Blade Devices, Tamper Resistant Duplex Receptacle,
Hubbell-Pro, Hospital Grade, 2-Pole 3-Wire Grounding, 15A 125V,
5-15R, Black

Features

- Tamper-resistant shutter complies with national electrical code requirements
- Triple wipe contacts
- High impact resistant face with circuit I.D. marking area
- Steel mounting strap

Application

Hubbell-Pro Heavy Duty Hospital Grade

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - UL 94V-2
- Environmental - Operating Temperature - Maximum continuous 75°C, minimum -40°C (w/o impact)
- Mechanical - Product Identification - Ratings are a permanent part of the device
- Mechanical - Terminal Accommodation - #14-#10 AWG copper stranded or solid conductor only
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

General

| | |
|------------------------------|---|
| Catalog Number | 8200BKTRA |
| EU RoHS Indicator | Contact Manufacturer |
| Horsepower - Maximum | 0.5 |
| Item Type | Traditional Duplex |
| Material | Nylon |
| Material - Mounting Hardware | Screw Mounting |
| Number Of Poles | 2-Pole |
| Operating Temperature | Maximum continuous 75°C and minimum -40°C without Impact |
| Series | Hubbell-Pro |
| Specifications | <ul style="list-style-type: none">• Automatic Self-groundingStaple - Stainless steel |



| | |
|-------|-------------------------------------|
| Style | Base - PBT |
| Type | Clamping Plate - Plated steel |
| UPC | Face - Nylon |
| | Ground Contacts - Brass |
| | Mounting Screws - Zinc plated steel |
| | Mounting Strap - Galvanized steel |
| | Power Contacts - Brass |
| | Smooth Face |
| | Receptacle |
| | 783585542096 |

Dimensions

| | |
|------------|-----------------------------|
| Dimensions | 3.28 in x 1.57 in x 1.15 in |
| Height | 1.15 in |
| Length | 3.28 in |
| Weight | 0.2 lb |
| Width | 1.57 in |

Electrical Ratings

| | |
|----------------------------|---------------------------|
| Amperage Rating | 15 A |
| Connectivity | Back and Side Wired |
| Current / Amperage Rating | 15 A |
| Current Rating | 15 A |
| Dielectric Strength | Withstands 2,000V minimum |
| Phase | Single Phase |
| Voltage Rating | 125 VAC |
| Voltage Rating Description | 125 V |
| Wattage | 1875 W |

Conductor Related

| | |
|-----------------|--------------------|
| Number Of Wires | 3-Wire |
| Wire Size | #14 AWG to #10 AWG |

Certifications And Compliance

| | |
|------------------------------------|--|
| Industry Standard(s) | <ul style="list-style-type: none">• Certified to CSA, C22.2, No. 42 File 285• Fed. Spec. W-C-596• NEMA® WD-6 Compliant• UL Listed to UL498 File No. E2186 |
| Nema Rating | 5-15R |
| Standards - RoHS Compliance Status | CM |

Logistics

| | |
|-----------------|----|
| Carton Quantity | 10 |
|-----------------|----|

Product Assets

- Catalog Page - WDK A-27 Catalog Page
- Catalog Page - WDK L-8 Catalog Page
- Catalogs - WDK Catalog Full 2024
- Literature - Tamper-Resistant Receptacles for Healthcare
- Literature - Heavy Duty Tamper-Resistant Receptacles
- Literature - Duct Products Guide
- Literature - Tamper-Resistant Receptacles
- Literature - Hubbell-Pro Hospital Grade Receptacles
- Literature - Hubbell-PRO Hospital Grade TR Receptacles
- Specifications - 8200BKTRA Specification Sheet French
- Specifications - 8200BKTRA Specification Sheet English
- Specifications - 8200BKTRA
- Warranty - Industrial & Commercial Products
- Video - Tamper-Resistant Receptacles
- Video - Tamper-Resistant Receptacles

