

HUBBELL
Wiring Device-Kellems

**EdgeConnect™, Straight Blade
Devices, Connector,
Industrial/Commercial Grade, 2-
Pole 3-Wire Grounding, 20A 125V,
5-20R, Black and White**

By Hubbell Wiring Device-Kellems
Catalog # [HBL5369CST](#)

EdgeConnect™, Straight Blade Devices, Connector,
Industrial/Commercial Grade, 2-Pole 3-Wire Grounding, 20A
125V, 5-20R, Black and White



Features

- Spring termination for a faster and more secure terminal connection
- Ribbed housing is impact and chemical resistant
- Superior cord grip design protects terminations from excess strain
- Accepts #14 - #10AWG, solid or stranded

General

Application	Extra Heavy Duty Industrial/Commercial Grade
Catalog Number	HBL5369CST
Color	Black and White
Cord Range	0.230"-0.720"(5.8-18.3)
EU RoHS Indicator	Contact Manufacturer
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	1
Insulation	Insulated Body
Item Type	Insulgrip® Connector
Material	Nylon
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact Electrical - Current Interrupting - Certified for current interrupting at full rated current Electrical - Dielectric Voltage - Withstands 2,000V minimum Environmental - Flammability - UL 94 V-2 Environmental - Operating Temperatures - Maximum continuous 75°C, minimum -40°C (w/o impact) Mechanical - Product Identification - Ratings are a permanent part of the device Mechanical - Terminal Accommodation - #14-#10 AWG copper stranded or solid conductor only Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA
Series	EdgeConnect™
Size	3.28 in x 1.41 in x 1.09 in
Style	Standard
Temperature Rating	Maximum continuous 75°C; minimum -40°C (w/o impact)
Type	Connectors
UPC	783585965383

Dimensions

Display Size	Standard Sized Product
Weight	0.2 lb

Electrical Ratings

Connectivity	Spring Termination
Current / Amperage Rating	20 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 V

Conductor Related

Conductor Range	#14 AWG to #10 AWG
Cord Type	All Listed Portables
Number Of Wires	3-Wire
Number of Conductors	3-Wire Grounding
Wire Size	#14 AWG to #10 AWG

Certifications And Compliance

Industry Standard(s)	CSA Certified to C22.2 No. 42 File 280 Fed. Spec. W-C596G NEMA® WD-6 Compliant UL Listed to UL498 File E1706
Nema Rating	5-20P

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Brochures - EdgeConnect Brochure](#)
[Brochures - EdgeConnect Brochure French](#)
[Catalog Page - WDK A-39 Catalog Page](#)
[Catalogs - WDK Catalog Full 2024](#)
[Installation Manuals - PD3069_Installation Manual](#)
[Literature - EdgeConnect™ Technology FAQ](#)
[Literature - EdgeConnect™ Termination vs Standard Push Wire](#)
[Literature - EdgeConnect™ Technology](#)
[Sales Drawings - M14757](#)
[Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WDK_CA-HBL5369CST-SPEC-EN | REV 6/2024