

Straight Blade Devices, Tamper  
Resistant Duplex Receptacle,  
Hospital Grade, Hubbell-Pro, LED  
Indicator, 20A 125V, 2-Pole 3-Wire  
Grounding, 5-20R

By Hubbell Wiring Device-Kellems  
Catalog # [8300LTRA](#)



Straight Blade Devices, Tamper Resistant Duplex Receptacle,  
Hospital Grade, Hubbell-Pro, LED Indicator, 20A 125V, 2-Pole 3-  
Wire Grounding, 5-20R, Brown

Features

- Tamper-resistant shutter complies with national electrical code requirements
- Green LED Power Indicators to identify emergency circuits
- Triple wipe contacts
- High impact resistant face with circuit I.D. marking area
- Steel mounting strap

Application

Hubbell-Pro Heavy Duty Hospital Grade

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - UL 94V-2
- Environmental - Operating Temperature - Maximum continuous 75°C, minimum -40°C (w/o impact)
- Mechanical - Product Identification - Ratings are a permanent part of the device
- Mechanical - Terminal Accommodation - #12-#10 AWG stranded or solid copper wire only
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

General

Catalog Number	8300LTRA
Horsepower - Maximum	1
Indicator(s) Type	Green LED
Item Type	Traditional Duplex
Material	Nylon
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Series	Hubbell-Pro

Specifications

- Automatic Self-grounding Staple - Stainless steel
- Base - PBT
- Clamping Plate - Plated steel
- Face - Nylon
- Ground Contacts - Brass
- Mounting Screws - Zinc plated steel
- Mounting Strap - Galvanized steel
- Power Contacts - Brass

Style  
Type  
UPC

Smooth Face  
Receptacle  
783585542331

Dimensions

Dimensions	3.28 in x 1.57 in x 1.15 in
Height	1.15 in
Length	3.28 in
Weight	0.2 lb
Width	1.57 in

Electrical Ratings

Amperage Rating	20 A
Connectivity	Back and Side Wired
Current / Amperage Rating	20 A
Current Rating	20 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 VAC
Voltage Rating Description	125 V
Wattage	2500 W

Conductor Related

Number Of Wires	3-Wire
Wire Size	#12 AWG to #10 AWG

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"><li>• Certified to CSA, C22.2, No. 42 File 285</li><li>• Fed. Spec. W-C-596</li><li>• NEMA® WD-6 Compliant</li><li>• UL Listed to UL498 File No. E2186</li></ul>
Nema Rating	5-20R

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- Catalog Page - WDK A-27 Catalog Page
- Catalog Page - WDK L-8 Catalog Page
- Catalogs - WDK Catalog Full 2024
- Literature - Tamper-Resistant Receptacles for Healthcare
- Literature - Duct Products Guide
- Literature - Hubbell-Pro Hospital Grade Receptacles
- Literature - Hubbell-PRO Hospital Grade TR Receptacles
- Literature - Healthcare Application Guide
- Specifications - 8300LTRA Specification Sheet
- Specifications - Wiring 8300LTRA Specification Sheet
- Specifications - 8300LTRA Specification Sheet French
- Warranty - Industrial & Commercial Products
- Video - Tamper-Resistant Receptacles
- Video - Tamper-Resistant Receptacles



A Hubbell brand