

Straight Blade Devices,
Receptacles, Tamper-Resistant
Duplex, 1/2 Load Controlled, 15A
125V, 2-Pole 3-Wire Grounding,
Back and Side Wired, Ivory

By Hubbell Wiring Device-Kellems
Catalog # [BR15C11TR](#)



Straight Blade Devices, Receptacles, Tamper-Resistant Duplex,
1/2 Load Controlled, 15A 125V, 2-Pole 3-Wire Grounding, Back
and Side Wired, Ivory

Features

- Permanently marked with universal power symbol and the word "CONTROLLED" to visually identify receptacles used in automatic energy management systems
- Patented TR design eliminates plug-in difficulty and TR complaints
- Markings can be read regardless of mounting orientation
- Complies with NEC Section 406.3, ASHRAE 90.1, and California Title 24 requirements
- Complements Hubbell's Load:Logic® control system or other available energy management system

Application

Commercial Specification Grade

Performance

- Electrical: Current Interrupting- Certified for current interrupting at full rated current
- Electrical: Dielectric Voltage- Withstands 2,000V minimum
- Mechanical: Product Identification- Ratings are a permanent part of the device
- Mechanical: Terminal Accommodation- #14-10 AWG stranded or solid copper wire only.
- Mechanical: Terminal Identification- Terminals identified in accordance with UL 498 and CSA
- Environmental: Flammability- UL 94V-2
- Environmental: Operating Temperature- Maximum continuous 75°C
- minimum -40°C (w/o impact)

General

Catalog Number	BR15C11TR
EU RoHS Indicator	Contact Manufacturer
Horsepower - Maximum	0.5
Item Type	Traditional Duplex
Material	Nylon
Number Of Poles	2-Pole

Operating Temperature

Maximum continuous 75°C and
minimum -40°C without Impact
Controlled

Series

Specifications

- Face: Nylon
- Base: Nylon
- Power Contacts: .030 in. (.8) Brass
- Ground Contacts: Brass
- Wire Clamp: .062 in. (1.6) Nickel plated steel:Mounting Strap: .040 in. Galvanized steel
- Automatic Self-grounding Staple: Stainless steel
- Mounting Screws: Galvanized Steel

Style

Type

UPC

Smooth Face

Tamper-Resistant

783585582450

Dimensions

Dimensions	3.28 in x 1.57 in x 1.07 in
Display Size	Standard Sized Product
Height	1.07 in
Length	3.28 in
Weight	0.2 lb
Width	1.57 in

Electrical Ratings

Amperage Rating	15 A
Connectivity	Back and Side Wired
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	1875 W

Conductor Related

Number Of Wires 3-Wire
Wire Size #14 AWG to #10 AWG

Certifications And Compliance

Industry Standard(s) UL Listed to UL498 File No.
 E2186Certified to CSA, C22.2,
 No. 42Fed. Spec. W-C-
 596NEMA® WD-6 Compliant

Logistics

Carton Quantity 10

Product Assets

- [Catalog Page - WDK A-24 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Literature - Tamper-Resistant Receptacles](#)
- [Literature - Automatic Receptacle Control Product Guide](#)
- [Specifications - BR15CI1TR Specification Sheet English](#)
- [Specifications - Wiring BR15CI1TR Specification Sheet](#)
- [Specifications - BR15CI1TR](#)
- [Warranty - Industrial & Commercial Products](#)
- [Video - Tamper-Resistant Receptacles](#)
- [Video - Tamper-Resistant Receptacles](#)

