



Straight Blade Devices, Male Inlets, Flanged, Industrial/Commercial, 20A 125V, 2-Pole 3-Wire Grounding, 5- 20P, White, Single Pack

By Hubbell Wiring Device-Kellems
Catalog # [HBL5378C](#)



Straight Blade Flanged Male Inlet 20A, 125V, 2-Pole, 3-Wire Grounding, 5- 20P.

Features

- Impact resistant thermoplastic construction
- Backwired terminations for ease of installation
- #8-32 Multiple drive terminal screws
- Mounting screws included

Application

Extra Heavy Duty Industrial

General

Color	<ul style="list-style-type: none"> • White • Blanc
Cord Range	0.230"-0.720" (5.8-18.3)
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	0.50
Insulation	Insulated Body
Item Type	Standard Single
Material	Nylon
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	<ul style="list-style-type: none"> • Electrical - Current Interrupting - Certified for current interrupting at full rated current • Electrical - Dielectric Voltage - Withstands 2,000V minimum • Environmental - Flammability - UL 94 V-2 • Environmental - Operating Temperatures - Maximum continuous 75°C minimum -40°C (w/o impact) • Mechanical - Product Identification - Ratings are a permanent part of the device

Dimensions

Dimensions	1.71 in x 1.69 in x 1.71 in
Display Size	Standard Sized Product
Height	1.71 in
Length	1.71 in
Weight	0.1 lb
Width	1.69 in

Electrical Ratings

Amperage Rating	20 A
Connectivity	Back Wired
Current / Amperage Rating	20 A
Current Rating	20 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 VAC
Voltage Rating Description	125 V
Wattage	2500 W

Conductor Related

Conductor Range	#18 AWG to #10 AWG
Number Of Conductors	3-Wire
Number Of Wires	3-Wire
Wire Size	#18 AWG to #10 AWG

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • Certified to CSA, C22.2, No. 42 • NEMA® WD-6 Compliant • UL Listed, File E2186
Nema Rating	5-20P
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - WDK A-39 Catalog Page](#)
[Catalog Page - WDK N-19 Catalog Page](#)
[Catalogs - WDK Catalog Full 2023](#)

- Mechanical - Terminal Accommodation - #18-#10 AWG copper stranded or solid conductor only
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

[Installation Manuals - WIRING_PD1279_INSTALLINST](#)
[Literature - Insulgrip® Straight Blade and Twist-Lock® Devices](#)
[Literature - Entertainment Product Solution Guide](#)
[Literature - Industrial Solutions](#)
[Sales Drawings - WDK_HBL5378C_DRAWING_PDF](#)
[Warranty - Industrial & Commercial Products](#)
[Video - Insulgrip Twist-Lock and Straight Blade Devices](#)

Series	Extra Heavy Duty
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact.
Type	<ul style="list-style-type: none">• Flanged Inlet• Flanged Inlet
UPC	783585174402



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WDK_CA-HBL5378C-SPEC-EN | REV 1/2024