




Straight Blade Devices, Receptacles, Duplex, Specification Grade, 2-Pole 3-Wire Grounding, 20A 250V, 6-20R, Gray, Single Pack

By Hubbell Wiring Device-Kellems
Catalog # [HBL5462GY](#)



HBL® Extra Heavy Duty MAX Straight Blade Duplex Receptacle
20A, 2-Pole 3-Wire Grounding, 250V, 6-20R.

Features

- Deep nylon body design delivers increased impact resistance
- One-piece brass integral ground strap
- Finder Groove Face
- Deep body design with circuit ID face

Application

Extra Heavy Duty

General

Color	<ul style="list-style-type: none"> • Gray • Gris
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	2
Item Type	Traditional Duplex
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	<ul style="list-style-type: none"> • Electrical - Current Interrupting - Certified for current interrupting at full rated current • Electrical - Dielectric Voltage - Withstands 2,000V minimum • Environmental - Flammability - Top: UL 94V-2, Base: UL 94V-0 • Environmental - Operating Temperatures - Maximum continuous 75°C minimum -40°C (w/o impact) • Mechanical - Product Identification - Ratings are a permanent part of the device • Mechanical - Terminal Accommodation - #14-#10

Dimensions

Dimensions	3.28 in x 1.65 in x 1.19 in
Display Size	Standard Sized Product
Height	1.19 in
Length	3.28 in
Weight	0.25 lb
Width	1.65 in

Electrical Ratings

Amperage Rating	20 A
Connectivity	Back and Side Wired Screw Terminals
Current / Amperage Rating	20 A
Current Rating	20 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	250 V
Voltage Rating Description	250 V
Wattage	5000 W

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #10 AWG

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • Certified to CSA 22.2, No. 42 File 285 • Guide RTRT Fed Spec WC596G • NEMA® WD-6 Compliant • UL Listed to UL498 File No. E2186
----------------------	---

Nema Rating	6-20R
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page](#) - [WDK A-12 Catalog Page](#)

AWG copper stranded or solid conductor only

- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

Catalogs - WDK Catalog Full 2023
Engineering Drawing - HBL5462GY AutoCAD Drawing
Installation Manuals - WIRING_PD2615_INSTALLINST
Literature - WIRING_WLFVM034
Literature - Pulp & Paper Solutions
Sales Drawings - WDK_HBL5462_DRAWING_PDF
Warranty - Industrial & Commercial Products

Series

Extra Heavy Duty

Style

Finder Groove Face

Type

- Standard Duplex
- Standard Duplex

UPC

783585435503



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WDK_CA-HBL5462GY-SPEC-EN | REV 1/2024