

Timer Switches, Single Pole,
8.3A120/277V AC, 30 Minute Delay
Time Out, White

By Hubbell Wiring Device-Kellems
Catalog # [DT5030W](#)

Timer Switches, Single Pole, 8.3A120/277V AC, 30 Minute Delay
Time Out, White

Features

- 30 minute timer
- Pre-set 5 button selection with permanent time markings
- Manual override to OFF
- Alert to OFF function - red LED will flash during the final 30 seconds
- Designed for use on 120 or 277V AC circuits

Performance

- Controls - 5 button selection - Preset time selection
- Controls - LED Indicators - Illuminates once time is selected
- Controls - OFF Switch - 6 seconds to 20 minutes (default set to 10 minutes)
- Electrical - Load Capacity - 120VAC 600W Incandescent, 5A Ballast, 5A CFL/LED 277V, Horsepower rating 1/6
- Environmental - Operating Temperature - 32°F to 122°F (0°C to 50°C) with rate of change not exceeding 20°F(11°C) per hour
- Environmental - Storage - -40°F to 150°F (-40°C to 65°C), 20% to 90% non condensing relative humidity

General

Catalog Number	DT5030W
Color	White
Control	Pre-Set 5 Button Selection
EU RoHS Indicator	No
Humidity	20% to 90% non-condensing relative humidity
Indicator	Illuminates once time is selected
Indicator(s) Type	Red LED
Item Type	Countdown Timer Wall Switch
Material	Polycarbonate
Operating Temperature	32°F to 122°F (0°C to 50°C) with rate of change not exceeding 20°F(11°C) per hour
Series	Fixed Countdown
Specifications	<ul style="list-style-type: none">• Housing - Polycarbonate• Mounting Bracket - Aluminum• Mounting Strap - Steel



Storage Temperature Range	-40°F to 150°F (-40°C to 65°C)
Timing Range	OFF, 5, 10,20, 30 minutes
UPC	783585256412

Dimensions

Dimensions	3.81 in x 1.75 in x 2.27 in
Height	2.27 in
Length	3.81 in
Width	1.75 in

Electrical Ratings

Connectivity	Wire Leads
Voltage Rating	120/277 VAC
Voltage Rating Description	120/277V AC
Wattage	1000/1400 W

Conductor Related

Wire Length	6 in
Wire Size	#14 AWG

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• cULus Listed To UL60730-1 And UL60730-2• Meets ASHRAE 90.1, and CEC Title 24 Compliant
----------------------	---

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[BIM - Lighting_Device-Count_Down_Timer-Hubbell_Wiring-DT5030W](#)
[Catalog Page - WDK Z-20 Catalog Page](#)
[Catalog Page - WDK E-6 Catalog Page](#)
[Catalogs - WDK Catalog Full 2024](#)
[Engineering Drawing - DT5030W AutoCAD Drawing](#)
[Installation Manuals - WIRING_PD2544_INSTALLINST](#)
[Literature - Multifamily Property Tech Enhancements](#)

Literature - Residential Catalog
Literature - Differentiate Your Property
Literature - Residential Product Guide
Literature - Property Management | Home Enhancements |
Innovation and Convenience

Sales Drawings - WDK_DT5030_DRAWING_PDF
Specifications - DT5030W Specification Sheet
Specifications - DT5030W Specification Sheet French
Specifications - Wiring DT5030W Specification Sheet
Warranty - HMOSS Occupancy Motion Sensors



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved
WDK_CA-DT5030W-SPEC-EN | REV 4/2025