



Surge Protective Devices, SPIKESHIELD TVSS Plug Strips, 15A 125V, 7 Outlet, 150 Joules, 6' Cord, Office White

By Hubbell Wiring Device-Kellems
Catalog Number [HBL7PS1050A](#)



Surge Protective Device SpikeShield® Plug Strip, 15A 125V, 7 Outlet, 1050 Joules, 6' Cord.

Features

- 1050 joule, 6 foot cord, \$5,000 down-line warranty
- Tamper tamper resistant shutters.
- Tamper resistant shutters

Application

7 Outlet, Standard Devices

General

Color	<ul style="list-style-type: none"> • Office White • Blanc cassé
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Indicator(s) Type	LED Indicator
Item Type	Surge Protection Plug Strips
Material	Non-Metallic
Material - Mounting Hardware	Portable
Number Of Outlets	7
Operating Temperature	32 Deg F to 140 Deg F (0 Deg C to 60 Deg C)
Outlet	Straight Blade 5-15R
Performance	<ul style="list-style-type: none"> • Electrical - Max Surge Current - 19.5kA • Electrical - Max. Operating Voltage - 130 • Electrical - Operating Frequency - 50/60Hz • Environmental - Operating Temperature - -40°F to 160°F (-40°C to 70°C)
Response Time	5
Series	Economy Surge Strips
Type	Non-Metallic
UPC	783585120553

Dimensions

Display Size 1050 Joules

Electrical Ratings

Connectivity	Plug-In
Current / Amperage Rating	15 A
Current Rating	15 A
Frequency Rating	60 Hz
Phase	Single Phase

Conductor Related

Cord Length 6 ft

Logistics

Carton Quantity 10

Product Assets

[Catalog Page - Wiring N-9 Catalog page](#)
[Engineering Drawing - HBL7PS1050A AutoCAD Drawing](#)
[Installation Manuals - WIRING_PD2380_INSTALLINST](#)
[Literature - SpikeShield® Power Quality Surge Protective Devices](#)
[Sales Drawings - WDK_HBL7PS1050A_DRAWING_PDF](#)
[Warranty - Surge Plug Strips](#)



A proud member of the Hubbell Family.

