

Heavy Duty Tamper-Resistant
AUTOGUARD® Self-Test GFCI
Combination Switch, 15A, Light
Almond

By Hubbell Wiring Device-Kellems
Catalog # [GFSPST15LA](#)



Power Protection Products, Receptacle, Self Test, GFCI and
Single Pole Switch, Commercial Grade, 15A 125V, 2- Pole 3-Wire
Grounding, 5-15R, Light Almond

Features

- Patented shutter design for tamper-resistant
- Compliant with NEC® 406.12 and NEC® 517-18(c)
- Patented AUTOGUARD® self test technology
- Triple wipe construction

General

Catalog Number	GFSPST15LA
Series	Heavy Duty
Specifications	• Base - Nylon • Face - Nylon • Ground Contacts - Brass • Mounting Screws - Zinc plated steel • Mounting Strap - Zinc plated steel • Power Contacts - Brass
Style	Combination Switch
UPC	883778124617

Electrical Ratings

Amperage Rating	15/15 A
Current / Amperage Rating	15 A

Voltage Rating Description	125 V
----------------------------	-------

Certifications And Compliance

Industry Standard(s)	Meets All NEC® Requirements
----------------------	-----------------------------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog Page - WDK Z-8 Catalog Page](#)
- [Catalog Page - WDK K-4 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Engineering Drawing - GFSPST15LA AutoCAD Drawing](#)
- [Installation Manuals - WIRING_PD2709_INSTALLINST](#)
- [Literature - AUTOGUARD® Self Test Ground Fault Receptacles](#)
- [Literature - Residential Product Guide](#)
- [Sales Drawings - WDK_GFSPST15_DRAWING_PDF](#)
- [Specifications - GFSPST15LA Specification Sheet](#)
- [Specifications - GFSPST15LA](#)
- [Specifications - Wiring GFSPST15LA Specification Sheet](#)
- [Warranty - Industrial & Commercial Products](#)
- [Video - Autoguard GFCI Receptacles](#)
- [Video - Autoguard GFCI Receptacles](#)
- [Video - Tamper-Resistant Receptacles](#)