

Kellems Wire Management,
Liquidtight System, Straight Male
Liquid Tight Connector, 3/8", Steel,
Non-Insulated

By Hubbell Wiring Device-Kellems
Catalog # [H038](#)

Kellems Wire Management, Liquidtight System, Straight Male
Liquid Tight Connector, 3/8", Steel, Non-Insulated

Features

- Hexagonal nut compresses gland-ring onto conduit
- Nylon gasket provides liquidtight seal at hub
- Non-integral steel ferrule seals conduit

Application

For use with Liquidtight Metal conduit and PolyTuff I Non-Metallic conduit

Performance

- Environmental - Operating Temperature - -60°F to +1000°F (-51°C to +538°C)
- Environmental - Hazardous Locations - NEC Reference -Class I, Div. 2 - 501-10(A)(3)B, Class II, Div. 1 - 502-10(A)(2), Class II, Div. 2 - 502-10(A)(3), Class III, Div. 1 - 503-10(A)(2), Class III, Div. 2 - 503-10(B)

General

Catalog Number	H038
EU RoHS Indicator	Contact Manufacturer
Material	Steel, Zinc Plated
Specifications	• Compression Nut - Zinc plated steel • Ferrule - Zinc plated steel • Fitting - Zinc plated steel • Locknut - Zinc plated steel • Split Seal Ring - Nylon • Washer - Nylon
Style	Straight



Type	Metallic Liquidtight Fittings
UPC	783585034010

Dimensions

Dimension - L Length Overall	1.437 in
mm	
Dimension - Thread Size	1/2"-14 NPT
Dimension - Width mm	1.062 in
Trade Size	3/8

Certifications And Compliance

Industry Standard(s)	• CSA Certified • UL 514B
----------------------	---

Logistics

Carton Quantity	50
-----------------	----

Product Assets

[Catalog Page - WDK W-90 Catalog Page](#)
[Catalog Page - WDK W-91 Catalog Page](#)
[Catalogs - WDK Catalog Full 2024](#)
[Engineering Drawing - H038 AutoCAD Drawing](#)
[Literature - Wire Management Solutions Brochure](#)
[Sales Drawings - WDK_H038_DRAWING_PDF](#)
[Specifications - H038 Specification Sheet French](#)
[Specifications - H038 Specification Sheet](#)
[Specifications - Wiring H038 Specification Sheet](#)
[Warranty - Industrial & Commercial Products](#)
[Video - Kellems Wire Management Solutions](#)
[Video - Kellems Wire Management Solutions](#)