

Industrial Grade, Motor  
Disconnect,Unfused,3 Pole, 30A 600V  
AC,Screw Terminals, IP69k,NEMA Type 4X,12  
Non-Metallic Sloped Top Enclosure for Top  
Feed Applications, inTOUCH Installation Free  
LED Phase Indication,Jog

By Hubbell Wiring Device-Kellems  
Catalog # [HBLDS30TPJ](#)

Industrial Grade, Motor Disconnect,Unfused,3 Pole, 30A 600V AC,Screw  
Terminals, IP69k,NEMA Type 4X,12, Non-Metallic Sloped Top Enclosure  
for Top Feed Applications, inTOUCH Installation Free LED Phase  
Indication,Jog

Features

- Constructed from corrosion and impact resistant UV stabilized non-metallic material
- Rounded sloped top enclosure has a single flat for top feed applications and supports best practices in hygienic design by shedding dirt and debris
- IP69k and Type 4X,12K water ingress protection and Certified by NSF for hygiene in food processing applications
- Highly visible red handle can be locked in the OFF position as a method of compliance with OSHA Lockout/Tagout requirements
- Product rating are permanently laser-marked and will not wash off
- Highly visible red handle can be locked in the OFF position as a method of compliance with OSHA Lockout/Tagout requirements
- Six highly visible integral phase identification LEDs for use on 3 Phase Y or Delta systems provide secondary means of visual confirmation of make/break on all phases

Application

Heavy Duty Industrial and/or Washdown

Performance

Electrical - Current Interrupting - Certified for current interrupting at full rated current & voltage, Electrical - Dielectric Voltage - Withstands 3000V AC minimum, Electrical - Max. Working Voltage - 600V AC RMS, Environmental - Flammability - UL94-5VA and V0 Classification, Environmental - Operating Temperature - Max Continuous 75°C,Min Continuous -40°C w/o impact, Environmental - UV Resistance - All materials are UV stabilized, Mechanical - Impact Resistance - In accordance with UL 746C, Mechanical - Mounting - Non-Metallic - External fully adjustable feet, Mechanical - Product Identification - Identification and ratings are part of external label, Mechanical - Terminal Identification - In accordance with UL, CSA and international conventions

Specifications

Industry Standard(s) cULus Listed  
Environmental Conditions Indoor and Outdoor

Conductor



|                              |                                                                                                                                                                                 |
|------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Wire Size                    | #14 AWG to #8AWG                                                                                                                                                                |
| Configuration                |                                                                                                                                                                                 |
| Mounting Method              | External fully adjustable feet                                                                                                                                                  |
| Current                      |                                                                                                                                                                                 |
| Dielectric Strength          | Withstands 3000V AC minimum                                                                                                                                                     |
| Current / Amperage Rating    | 30 A                                                                                                                                                                            |
| Dimensions                   |                                                                                                                                                                                 |
| Weight                       | 2.9 lb.                                                                                                                                                                         |
| Height                       | 4.12 in                                                                                                                                                                         |
| Hub Size                     | 3/4"                                                                                                                                                                            |
| General                      |                                                                                                                                                                                 |
| Specifications               | <ul style="list-style-type: none"><li>Base - Valox®</li><li>Enclosure Gasket - Neoprene</li><li>Handle - Valox®</li><li>Shaft (Unfused) - Valox®</li><li>Top - Valox®</li></ul> |
| Color                        | Gray                                                                                                                                                                            |
| Style                        | Heavy Duty                                                                                                                                                                      |
| Ingress Protection           | IP69k, NEMA Type 4X, 12                                                                                                                                                         |
| UPC                          | 783585763552                                                                                                                                                                    |
| Type                         | Disconnect Switches                                                                                                                                                             |
| Material - Mounting Hardware | Stainless Steel Screw Mounting                                                                                                                                                  |
| Enclosure Type               | IP69k and UL Type 4X, 12                                                                                                                                                        |
| Series                       | Non-Fused                                                                                                                                                                       |
| Logistics                    |                                                                                                                                                                                 |
| Pallet Quantity              | 1                                                                                                                                                                               |
| Carton Quantity              | 1                                                                                                                                                                               |

Operational

Operating Cycles 10,000 Cycles Minimum  
Operating Temperature Without Impact Maximum  
continuous 75°C and minimum -40 °C

[Catalog Page \[English\]](#)

[Installation Manual \[English\]](#)

