



Locking Devices, Hubbellock, Industrial, Female Connector Body, 20A 125V, 2-Pole 3-Wire Grounding, Non-NEMA, Screw Terminal, Black and White

By Hubbell Wiring Device-Kellems
Catalog # [HBL23032B](#)



Hubbellock® Industrial Female Connector Body, 20A 125V, 2-Pole 3-Wire Grounding housing, Thermoset interior, Non-NEMA, Screw Terminal.

Features

- Spring loaded safety shutter contains arcing when mating or un-mating devices under load
- Spring loaded safety shutter automatically ejects the plug eliminating contact teasing
- Box terminals in conjunction with screws with pressure pads provide maximum termination strength and dependability
- Three-piece clamp assembly provides maximum strain relief and protects against entry of moisture and dust

Application

Heavy Duty Industrial

General

Color	Black
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	20A Grounding Hubbellock® Female Connector
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
Performance	<ul style="list-style-type: none"> • Electrical - Current Interrupting - Certified for current interrupting at full rated current • Electrical - Dielectric Voltage Withstand - 2,000V minimum • Environmental - Flammability - HB or better • Environmental - Moisture Resistance - IP30 Suitability • Environmental - Operating Temperatures - Maximum Continuous 75°C, Minimum -40°C (w/o impact) • Mechanical - Terminal Accommodation - #16

Dimensions

Dimensions	1.63 in x 1.72 in x 3.56 in
Display Size	Standard
Height	3.56 in
Length	1.63 in
Weight	0.35 lb
Width	1.72 in

Electrical Ratings

Amperage Rating	20 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	20 A
Current Rating	20 A
Voltage Rating	125 V
Voltage Rating Description	125 V

Conductor Related

Cable Range	0.320 - 0.660 in
Number Of Wires	3-Wire
Wire Size	#16 AWG to #12 AWG

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • Certified to CSA C22.2 No.42 • Listed to UL 498
----------------------	--

Logistics

Carton Quantity	20
-----------------	----

Product Assets

[Catalog Page - WDK B-62 Catalog Page](#)
[Catalog Page - WDK K-19 Catalog Page](#)
[Catalogs - WDK Catalog Full 2023](#)
[Installation Manuals - WIRING_PD1159_INSTALLINST](#)
[Sales Drawings - WDK_HBL23032B_DRAWING_PDF](#)
[Warranty - Industrial & Commercial Products](#)

AWG - #12 AWG stranded
copper wire only.

- Mechanical - Terminal
Identification - Terminals
identified in accordance
with UL 498

Type

- Connector Body
- Connector Body

UPC

783585017556



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WDK_CA-HBL23032B-SPEC-EN | REV 1/2024