



Industrial Grade, Disconnect Switches, Unfused Switch, Three Pole, 30A 600V AC, Screw Terminals, NEMA4XEnclosure, With Aux Contact

By Hubbell Wiring Device-Kellems
 Catalog # [HBLDS3ACNK](#)



Switches and Lighting Controls, Industrial Grade, Disconnect Switches, Unfused Switch, Three Pole, 30A 600V AC, Screw Terminals, Gray, NEMA4XEnclosure, With Aux Contact.

Features

- Constructed from corrosion and impact resistant UV stabilized non-metallic material
- IP69k and Type 4X,12K water ingress protection
- Certified by NSF for hygiene in food processing applications
- Highly visible red handle which meets OSHA Lockout/Tagout capabilities
- Reversible interior accomodates top or bottom conduit opening

Application

Labelless

General

Enclosure Type	Type 4X, IP69k
Mounting Method	External fully adjustable feet
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact

Performance	<ul style="list-style-type: none"> • Electrical - Current Interrupting - Certified for current interrupting at full rated current & voltage • Electrical - Dielectric Voltage - Withstands 3000V AC minimum • Electrical - Max. Working Voltage - 600V AC RMS • Environmental - Flammability - UL94-5VA and V0 Classification • Environmental - Operating Temperature - Max Continuous 75°C,Min Continuous -40°C w/o impact • Environmental - UV Resistance - All materials are UV stabilized • Mechanical - Impact Resistance - In accordance
-------------	---

Dimensions

Dimensions	8.5 in x 6 in x 4.12 in
Height	4.12 in
Length	8.5 in
Width	6 in

Electrical Ratings

Amperage Rating	30 A
Current / Amperage Rating	30 A
Current Rating	30 A
Dielectric Strength	Withstands 3000V AC minimum

Certifications and Compliance

Industry Standard(s)	UL Listed
----------------------	-----------

Logistics

Carton Quantity	1
-----------------	---

Product Assets

- [Catalog Page - WDK F-5 Catalog Page](#)
- [Catalog Page - WDK F-17 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2023](#)
- [Installation Manuals - WIRING_PD1782_PD1789_INSTALLINST](#)
- [Literature - Circuit-Lock® Motor Disconnects](#)
- [Literature - Improved Short Circuit Current Ratings \(SCCR\)](#)
- [Warranty - Industrial & Commercial Products](#)

with UL 746C

- Mechanical - Mounting - Non-Metallic - External fully adjustable feet
- Mechanical - Product Identification - Identification and ratings are part of external label
- Mechanical - Terminal Identification - In accordance with UL, CSA and international conventions

Series
Style
Type

Non-Fused
Heavy Duty

- Disconnect Switches
- Disconnect Switches

UPC

783585003771



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WDK_CA-HBLDS3ACNK-SPEC-EN | REV 1/2024