



# Locking Devices, Twist-Lock®, Industrial, Male Plug, 20A 125V, 2-Pole 3-Wire Grounding, L5-20P, Screw Terminal, Black and White

By Hubbell Wiring Device-Kellems  
Catalog # [HBL2311](#)



Twist-Lock® Industrial Insulgrip® 20A Male Plug, 125V NEMA L5-20P, 2-Pole, 3-Wire Grounding/White.

## Features

- Ribbed nylon housing provides a secure grip and impact and chemical resistance.
- Superior cord grip design protects terminations from excess strain.
- Clear, funnel shaped wire entry for ease of termination.
- Integral dust shield protects wiring chamber from dust or contaminants.

## Application

Extra Heavy Duty Industrial

## General

Color	Noir, blanc
Cord Range	0.360"-0.930" (9-24)
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	1
Item Type	20A Male Insulgrip® Plug
Material	Nylon
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	<ul style="list-style-type: none"> <li>• Electrical - Current Interrupting - Certified for current interrupting at full rated current</li> <li>• Electrical - Dielectric Voltage - Withstands 2,000V minimum</li> <li>• Environmental - Flammability - HB or better per UL94 or CSA 22.2 No. 0.6</li> <li>• Environmental - Moisture Resistance - IP20 Suitability</li> <li>• Environmental - Operating Temperatures - Maximum Continuous 75°C Minimum -40°C (w/o impact)</li> <li>• Mechanical - Terminal</li> </ul>

## Dimensions

Dimensions	2.26 in x 2.26 in x 2.75 in
Display Size	Standard Sized
Height	2.75 in
Length	2.26 in
Weight	0.25 lb
Width	2.26 in

## Electrical Ratings

Amperage Rating	20 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	20 A
Current Rating	20 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 VAC
Voltage Rating Description	125 VAC

## Conductor Related

Cable Range	0.360 - 0.930 in
Cord Type	All Listed Portables
Number Of Wires	3-Wire
Wire Size	#16 AWG to #8 AWG

## Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> <li>• Certified to CSA C22.2 No.42</li> <li>• Fed.Spec. W-C-596</li> <li>• Listed to UL 498</li> </ul>
----------------------	---

Nema Rating	L5-20P
Standards - RoHS Compliance Status	CM

## Logistics

Carton Quantity	30
-----------------	----

## Product Assets

[Catalog Page - WDK B-20](#) [Catalog Page - WDK B-42](#) [Catalog Page - WDK Catalog Full 2023](#)  
[Engineering Drawing - HBL2311](#) [AutoCAD Drawing - WIRING\\_PD1651\\_INSTALLINST](#)  
[Literature - Food Processing Guide](#)

	Accommodation - #16 AWG - #8 AWG stranded copper wire only.	<a href="#">Literature - Insulgrip® Straight Blade and Twist-Lock® Devices</a> <a href="#">Literature - Healthcare Application Guide</a> <a href="#">Literature - Industrial Solutions</a> <a href="#">Literature - Education Application Guide</a> <a href="#">Literature - Wiring Device Solutions for Strategic Manufacturing Facilities</a> <a href="#">Literature - Emergency Preparedness for Healthcare</a> <a href="#">Literature - Entertainment Product Solution Guide</a> <a href="#">Sales Drawings - WDK_HBL2311_DRAWING_PDF</a> <a href="#">Warranty - Industrial &amp; Commercial Products</a>
Type	<ul style="list-style-type: none"> <li>Mechanical - Terminal Identification - Terminals identified in accordance with UL 498</li> <li>Plugs</li> <li>Plugs</li> </ul>	<a href="#">Video - Insulgrip Twist-Lock and Straight Blade Devices</a> <a href="#">Video - Twist-Lock Devices</a>
UPC	783585037707	



**A proud member of the Hubbell Family.**

©2024 Hubbell Incorporated. All rights reserved.  
 WDK\_CA-HBL2311-SPEC-EN | REV 1/2024