



# Switches and Lighting Controls, Industrial Grade, Disconnect Switches, Unfused Switch, Three Pole, 30A 600V AC, Screw Terminals, Gray, No Knockouts

By Hubbell Wiring Device-Kellems  
Catalog # [HBLDS3NK](#)



Circuit-Lock® Disconnect Switch Enclosure 30A, Without  
Conduit Knockout or Fitting.

## Features

- Molded-in conduit opening and field installed hub
- Internal frame automatically bonds all grounds
- Reversible interior accommodates top or bottom conduit opening
- Constructed from corrosion and impact resistant UV stabilized non-metallic material
- IP69k and Type 4X,12K water ingress protection
- Certified by NSF for hygiene in food processing applications
- Highly visible red handle which meets OSHA Lockout/Tagout capabilities
- Reversible interior accomodates top or bottom conduit opening

## Application

Labelless

## General

Color	<ul style="list-style-type: none"> <li>• Gray</li> <li>• Gris</li> </ul>
Enclosure Type	Type 4X, IP69k
Mounting Method	External fully adjustable feet
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	<ul style="list-style-type: none"> <li>• Electrical - Current Interrupting - Certified for current interrupting at full rated current &amp; voltage</li> <li>• Electrical - Dielectric Voltage - Withstands 3000V AC minimum</li> <li>• Electrical - Max. Working Voltage - 600V AC RMS</li> <li>• Environmental - Flammability - UL94-5VA and VO Classification</li> <li>• Environmental - Operating Temperature - Max Continuous 75°C,Min</li> </ul>

## Dimensions

Dimensions	8.5 in x 6 in x 4.12 in
Height	4.12 in
Length	8.5 in
Width	6 in

## Electrical Ratings

Amperage Rating	30 A
Current / Amperage Rating	30 A
Current Rating	30 A
Dielectric Strength	Withstands 3000V AC minimum

## Certifications and Compliance

Industry Standard(s)	UL Listed
----------------------	-----------

## Logistics

Carton Quantity	1
-----------------	---

## Product Assets

[Catalog Page - WDK F-5 Catalog Page](#)  
[Catalog Page - WDK F-17 Catalog Page](#)  
[Catalogs - WDK Catalog Full 2023](#)  
[Engineering Drawing - HBLDS3NK AutoCAD Drawing](#)  
[Installation Manuals - WIRING\\_PD1782\\_INSTALLINST](#)  
[Literature - Circuit-Lock® Motor Disconnects](#)  
[Literature - Improved Short Circuit Current Ratings \(SCCR\)](#)  
[Sales Drawings - WDK\\_HBLDS3NK\\_DRAWING\\_PDF](#)  
[Warranty - Industrial & Commercial Products](#)

Continuous -40°C w/o impact

- Environmental - UV Resistance - All materials are UV stabilized
- Mechanical - Impact Resistance - In accordance with UL 746C
- Mechanical - Mounting - Non-Metallic - External fully adjustable feet
- Mechanical - Product Identification - Identification and ratings are part of external label
- Mechanical - Terminal Identification - In accordance with UL, CSA and international conventions

Series

Non-Fused

Style

Heavy Duty

Type

- Disconnect Switches
- Disconnect Switches

UPC

783585841014



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
WDK\_CA-HBLDS3NK-SPEC-EN | REV 1/2024