



Locking Devices, Twist-Lock®, Safety Shroud, Angled Receptacle, 30A 125V, 2-Pole 3-Wire Grounding, L5-30R, Screw Terminal, Gray

By Hubbell Wiring Device-Kellems
Catalog # [HBL2610AR](#)



Twist-Lock® Safety-Shroud®, Angled Receptacle, 1-Gang, 30A 125V AC, 2-Pole 3-Wire Grounding, NEMA L5, Screw Terminal.

Features

- Alignment arrows with lock and unlock symbols provide a visual indication that devices are properly connected
- Catalog number and color coded voltage rating are visible even when in use
- Engineered thermoplastic housing is impact and corrosion resistant, making it suitable for heavy-duty industrial environments

Application

Heavy Duty Industrial Shrouded

General

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	2
Item Type	30A Safety-Shroud® Receptacle
Material	Valox™
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Number of Gang(s)	1-Gang
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	<ul style="list-style-type: none"> • Electrical - Current Interrupting - Certified for current interrupting at full rated current • Electrical - Dielectric Voltage - Withstands 2,000V minimum • Environmental - Flammability - V2 or better per UL94/CSA 22.2 No.0.17 • Environmental - Moisture Resistance - IP20 Suitability • Environmental - Operating Temperatures - Maximum Continuous 75°C, Minimum -40°C (w/o impact) • Mechanical - Terminal

Dimensions

Dimensions	4.77 in x 2.85 in x 3.14 in
Display Size	Standard Sized Product
Height	3.14 in
Length	4.77 in
Weight	0.70 lb
Width	2.85 in

Electrical Ratings

Amperage Rating	30 A
Connectivity	Back Wired Screw Terminals
Current / Amperage Rating	30 A
Current Rating	30 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V

Conductor Related

Number Of Wires	3-Wire
Wire Size	#16 AWG to #8 AWG

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • Certified to CSA C22.2 No.42 • Fed.Spec. W-C-596 • Listed to UL 498
----------------------	---

Nema Rating	L5-30R
-------------	--------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - WDK B-29 Catalog Page](#)
[Catalogs - WDK Catalog Full 2023](#)
[Engineering Drawing - HBL2610AR AutoCAD Drawing](#)
[Installation Manuals - WIRING_PD1291_INSTALLINST](#)
[Sales Drawings - WDK_HBL2610AR_DRAWING_PDF](#)
[Warranty - Industrial & Commercial Products](#)
[Video - Insulgrip Twist-Lock and Straight Blade Devices](#)
[Video - Twist-Lock Devices](#)

Accommodation - #16
AWG - #8 AWG solid or
stranded copper wire only.

- Mechanical - Terminal
Identification - Terminals
identified in accordance
with UL 498

Type

- Receptacle
- Receptacle

UPC

783585234243

Related Products

[HBL2611S - Locking Devices, Twist-Lock®, Safety Shroud, Male Plug, 30A 125V, 2-Pole 3-Wire Grounding, L5-30P, Screw Terminal, Black and White](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WDK_CA-HBL2610AR-SPEC-EN | REV 1/2024