

Locking Devices, Twist-Lock®,
Industrial, Reversed Service Female
Connector Body, 30A 125/250V,
L14-30R

By Hubbell Wiring Device-Kellems
Catalog # [HBL2713SR](#)

Locking Devices, Twist-Lock®, Industrial, Reversed Service
Female Connector Body, 30A 125/250V, 3-Pole 4-Wire
Grounding, L14-30R, Screw Terminal, Black and White.

Features

- Alignment arrows with lock and unlock symbols provide a visual indication that devices are properly connected
- Superior cord grip design protects terminations from excess strain
- UL Type 4X Environmental seal protects connection while in use.

Application

Heavy Duty Industrial

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - HB or better per UL94/CSA 22.2 No.0.17
- Environmental - Moisture Resistance - IP20 Suitability
- Environmental - Operating Temperatures - Maximum Continuous 75°C, Minimum -40°C (w/o impact)
- Mechanical - Terminal Accommodation - #16 AWG - #8 AWG stranded copper wire only.
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498

General

Catalog Number	HBL2713SR
Cord Range	0.350"-1.150" (9-29)
EU RoHS Indicator	Yes
Environmental Conditions	Watertight
Insulation	Insulated Body
Item Type	30A Watertight Safety-Shroud® Reverse Service Connector
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	3-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact



Specifications

- Assembly Screws - Stainless Steel
 - Contacts - Brass
 - Housing / Cord Clamp - PBT
 - Terminal Clamp - Cold rolled steel – nickel plated
 - Terminal Retainer - Clear polycarbonate
 - Terminal Screws - #10-32 Brass (Phillips / Slotted / Robertson)
 - Watertight Gland - Neoprene
- Device
783585231792

Type
UPC

Dimensions

Dimensions	2.94 in x 2.94 in x 5.5 in
Display Size	Standard
Height	5.5 in
Length	2.94 in
Width	2.94 in

Electrical Ratings

Amperage Rating	30 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	30 A
Current Rating	30 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125/250 VAC
Voltage Rating Description	125/250 VAC

Conductor Related

Cable Range	0.350 - 1.150 in
Number Of Wires	4-Wire
Wire Size	#16 AWG to #8 AWG

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• Certified to CSA C22.2 No.42• Fed.Spec. W-C-596• Listed to UL 498
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- Catalog Page - WDK H-13 Catalog Page
- Catalog Page - WDK B-31 Catalog Page

- Catalog Page - WDK B-41 Catalog Page
- Catalogs - WDK Catalog Full 2024
- Engineering Drawing - HBL2713SR AutoCAD Drawing
- Installation Manuals - WIRING_PD1992_INSTALLINST
- Literature - PULP & PAPER SOLUTIONS
- Literature - Pulp & Paper Solutions
- Sales Drawings - WDK_HBL2713SR_DRAWING_PDF
- Specifications - HBL2713SR Specification Sheet
- Specifications - HBL2713SR Specification Sheet French
- Specifications - Wiring HBL2713SR Specification Sheet
- Warranty - Industrial & Commercial Products
- Video - Insulgrip Twist-Lock and Straight Blade Devices
- Video - Insulgrip Twist-Lock and Straight Blade Devices
- Video - Twist-Lock Devices

