

Switches and Motor Controls, Industrial
Grade, Disconnect Switches, Unfused
Switch, Three Pole, 60A 600V AC,
Stainless Steel, NEMA 4X Enclosure

By Hubbell Wiring Device-Kellems
Catalog # [HBLDS6SSAC](#)

Switches and Motor Controls, Industrial Grade, Disconnect
Switches, Unfused Switch, Three Pole, 60A 600V AC, Screw
Terminals, Stainless Steel, NEMA 4X Enclosure, With Aux Contact

Features

- Formed in nonporous 304 stainless steel
- IP69k and Type 4X,12K water ingress protection
- Certified by NSF for hygiene in food processing applications
- Highly visible red handle which meets OSHA Lockout/Tagout capabilities
- Accepts up to 2 Auxiliary contacts

Application

Labelless

Performance

Electrical - Current Interrupting - Certified for current interrupting at full rated current & voltage, Electrical - Dielectric Voltage - Withstands 3000V AC minimum, Electrical - Max. Working Voltage - 600V AC RMS, Environmental - Flammability - UL94-5VA and V0 Classification, Environmental - Operating Temperature - Max Continuous 75°C,Min Continuous -40°C w/o impact, Environmental - UV Resistance - All materials are UV stabilized, Mechanical - Impact Resistance - In accordance with UL 746C, Mechanical - Mounting - Stainless Steel - Feet are fixed, Mechanical - Product Identification - Identification and ratings are part of external label, Mechanical - Terminal Identification - In accordance with UL, CSA and international conventions

Specifications

Standards - RoHS Compliance	CM
Status	
EU RoHS Indicator	Yes
Industry Standard(s)	UL Listed

Configuration

Mounting Method	Feet are fixed
-----------------	----------------

Current

Amperage Rating	60 A
Dielectric Strength	Withstands 3000V AC minimum



Current Rating	60 A
Phase	Three Phase
Current / Amperage Rating	60 A

Dimensions

Length	11.63 in
Height	5.39 in
Width	7.3 in
Dimensions	11.63 in x 7.3 in x 5.39 in

General

Style	Heavy Duty
Ingress Protection	IP69K
Enclosure Type	Type 4X, IP69k
Series	Non-Fused
Specifications	• Base - #14 Gauge Type 304 Stainless Steel • Enclosure Gasket - Neoprene • Handle - Valox® • Shaft (Unfused) - Valox® • Top - #14 Gauge Type 304 Stainless Steel
UPC	783585372570
Type	Disconnect Switches

Logistics

Carton Quantity	1
-----------------	---

Operational

Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
-----------------------	--

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)
[Catalog Page \[English\]](#)
[Installation Manual \[Spanish, French, English\]](#)