

Straight Blade Devices,
Receptacles, Decorator Duplex,
Commercial Grade, Corrosion
Resistant, Smooth Face, 15A 125V,
2- Pole 3-Wire Grounding, 5-15R.

By Hubbell Wiring Device-Kellems
Catalog # IG15DRGRY



Straight Blade Devices, Receptacles, Decorator Duplex,
Commercial Grade, Corrosion Resistant, Smooth Face, 15A 125V,
2- Pole 3-Wire Grounding, 5-15R, Back and Side Wired, Gray.

Features

- Triangle marking on face indicates isolated ground
- Aesthetic Style Line® decorator design
- Triple wipe contacts

Application

Commercial Grade

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - UL 94 V-2
- Environmental - Operating Temperatures - Maximum continuous 75°C minimum -40°C (w/o impact)
- Mechanical - Product Identification - Ratings are a permanent part of the device
- Mechanical - Terminal Accommodation - #14-#10 AWG copper stranded or solid conductor only
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

General

Catalog Number	IG15DRGRY
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	0.5
Item Type	Decorator Duplex
Material	Nylon
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Series	Commercial Specification Grade

Specifications

- Automatic Self-grounding Staple - Stainless steel
 - Base - Nylon
 - Face - Nylon
 - Ground Contacts - Brass
 - Mounting Screws - Galvanized Steel
 - Mounting Strap - .040 in. (1) Galvanized steel
 - Power Contacts - .030 in. (.8) Brass
 - Terminal Screws - Plated steel
 - Wire Clamp - .062 in. (1.6) Nickel plated steel
- Style Line Decorator
Standard Duplex
783585146881

Style
Type
UPC

Dimensions

Dimensions	1.29 in x 0.83 in x 3.28 in
Display Size	Standard Sized Product
Height	3.28 in
Length	1.29 in
Weight	0.15 lb
Width	0.83 in

Electrical Ratings

Amperage Rating	15 A
Connectivity	Back and Side Wired Screw Terminals
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	1875 W

Conductor Related

Number Of Wires 3-Wire
Wire Size #14 AWG to #10 AWG

Certifications And Compliance

Industry Standard(s)

- Certified to CSA C22.2, No. 42
- Fed. Spec. WC596
- NEMA® WD-6 Compliant
- UL Listed to UL498 File No. E2186

Nema Rating 5-15R

Logistics

Carton Quantity 10

Product Assets

[Catalog Page - WDK M-18 Catalog Page](#)
[Catalog Page - WDK A-30 Catalog Page](#)
[Catalogs - WDK Catalog Full 2024](#)
[Engineering Drawing - IG15DRGRY AutoCAD Drawing](#)
[Installation Manuals - WIRING_PD1579_PD2305_INSTALLINST](#)
[Sales Drawings - WDK_IG15DRGRY_DRAWING_PDF](#)
[Specifications - IG15DRGRY Specification Sheet](#)
[Specifications - IG15DRGRY Specification Sheet French](#)
[Specifications - Wiring IG15DRGRY Specification Sheet](#)
[Warranty - Industrial & Commercial Products](#)

