



Wiring Device-Kellems

# Locking Devices, Twist-Lock®, Industrial, Flanged Inlet, 30A 125/250V, 3-Pole 4-Wire Grounding, L14-30P, Screw Terminal, White

By Hubbell Wiring Device-Kellems  
Catalog # [HBL2715](#)



Twist-Lock® Industrial 30A Flanged Inlet, 125/250V, 3-Pole, 4-Wire Grounding, L14-30P.

## Features

- Backwired terminations for ease of installation
- #10-32 Multiple drive terminal screws (Slotted, Phillips, Robertson)
- Mounting screws included
- Back wired terminations for ease of installation

## Application

Extra Heavy Duty Industrial

## General

Color	White
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	30A Grounding Insulgrip® Flanged Inlet
Material	Nylon
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	<ul style="list-style-type: none"> <li>• Electrical - Current Interrupting - Certified for current interrupting at full rated current</li> <li>• Electrical - Dielectric Voltage - Withstands 2,000V minimum</li> <li>• Environmental - Flammability - HB or better per UL94/CSA 22.2 No.0.17</li> <li>• Environmental - Moisture Resistance - IP20 Suitability</li> <li>• Environmental - Operating Temperatures - Maximum Continuous 75°C. Minimum -40°C (w/o impact)</li> <li>• Mechanical - Terminal Accommodation - #16 AWG - #8 AWG solid or</li> </ul>

## Electrical Ratings

Amperage Rating	30 A
Connectivity	Back Wired Screw Terminals
Current / Amperage Rating	30 A
Current Rating	30 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125/250 VAC
Voltage Rating Description	125/250 VAC

## Conductor Related

Number Of Wires	4-Wire
Wire Size	#16 AWG to #8 AWG

## Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> <li>• Certified to CSA C22.2 No.42</li> <li>• Fed.Spec. W-C-596</li> <li>• Listed to UL 498</li> </ul>
----------------------	---

Nema Rating	L14-30P
Standards - RoHS Compliance Status	CM

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

- [Catalog Page - WDK N-19 Catalog Page](#)
- [Catalog Page - WDK B-30 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2023](#)
- [Engineering Drawing - HBL2715 AutoCAD Drawing](#)
- [Installation Manuals - WIRING\\_PD1258\\_INSTALLINST](#)
- [Literature - Insulgrip® Straight Blade and Twist-Lock® Devices](#)
- [Literature - Wiring Device Solutions for Strategic Manufacturing Facilities](#)
- [Literature - Emergency Preparedness for Healthcare](#)
- [Literature - Entertainment Product Solution Guide](#)
- [Sales Drawings - WDK\\_HBL2715\\_DRAWING\\_PDF](#)
- [Warranty - Industrial & Commercial Products](#)
- [Video - Insulgrip Twist-Lock and Straight Blade Devices](#)
- [Video - Twist-Lock Devices](#)

## Related Products

AWS - #0 AWS solid or  
stranded copper wire only.

- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498

- Flanged Inlet

- Flanged Inlet

783585039190

WP2 - Wallplates and Boxes, Weatherproof Covers, 1-Gang, For Large Flanged Devices, Standard Size, Reinforced thermoplastic polyester

HBL2713 - Locking Devices, Twist-Lock®, Industrial, Female Connector Body, 30A 125/250V, 3-Pole 4-Wire Grounding, L14-30R, Screw Terminal, Black and White

HBL2713BK - Locking Devices, Twist-Lock®, Insulgrip® Connector, 30A, 125/250V AC, 3 Pole, 4 Wire Grounding, NEMA L14-30R, Black nylon

Type

UPC

## Dimensions

Dimensions	3.06 in x 3.06 in x 2.27 in
Display Size	Standard Sized Product
Height	2.27 in
Length	3.06 in
Weight	0.25 lb
Width	3.06 in



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
WDK\_CA-HBL2715-SPEC-EN | REV 1/2024