

Locking Devices, Twist-Lock®,
Industrial, Flanged Receptacle, 30A,
3-Phase Y, 120/208V AC, 4-Pole 4-
Wire Non- Grounding, L18-20R,
Screw Terminal

By Hubbell Wiring Device-Kellems
Catalog # [HBL2756](#)

Locking Devices, Twist-Lock®, Industrial, Flanged Receptacle,
30A, 3-Phase Y, 120/208V AC, 4-Pole 4-Wire Non- Grounding,
L18-20R, Screw Terminal, White

Features

- Impact resistant thermoplastic construction
- Backwired terminations for ease of installation
- #10-32 Multiple drive terminal screws (Slotted, Phillips, Robertson)
- Mounting screws included

Application

Insulgrip

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - V2 or better per UL94/CSA 22.2 No.0.17
- Environmental - Moisture Resistance - IP20 Suitability
- Environmental - Operating Temperatures - Maximum Continuous 75°C Minimum -40°C (w/o impact)
- Mechanical - Terminal Accommodation - #16 AWG - #8 AWG solid or stranded copper wire only.
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498

General

Catalog Number	HBL2756
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	2
Item Type	30A Non- Grounding Insulgrip® Flanged Receptacle
Material	Nylon
Material - Mounting Hardware	Screw Mounting
Number Of Poles	4-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact

Specifications

Type	Assembly Screws - Steel - nickel plated
UPC	Contacts - Brass
	Housing - Nylon
	Mounting Screw - Nickel plated brass
	Terminal Clamp - Cold rolled steel – nickel plated
	Terminal Retainer - Clear polycarbonate
	Terminal Screws - #10-32 Brass (Phillips / Slotted / Robertson)
	Flanged Receptacle
	783585039466

Dimensions

Dimensions	3.06 in x 3.06 in x 2.27 in
Display Size	Standard Sized Product
Height	2.27 in
Length	3.06 in
Weight	0.4 lb
Width	3.06 in

Electrical Ratings

Amperage Rating	30 A
Connectivity	Back Wired Screw Terminals
Current / Amperage Rating	30 A
Current Rating	30 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Three Phase
Voltage Rating	3 Phase WYE 120/208 VAC
Voltage Rating Description	3 Phase WYE 120/208 VAC

Conductor Related

Number Of Wires	4-Wire
Wire Size	#16 AWG to #8 AWG



Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">Certified to CSA C22.2 No.42Fed.Spec. W-C-596Listed to UL 498
Nema Rating	L18-30R
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- Catalog Page - WDK N-19 Catalog Page
- Catalog Page - WDK B-36 Catalog Page
- Catalogs - WDK Catalog Full 2024
- Engineering Drawing - HBL2756 AutoCAD Drawing
- Installation Manuals - WIRING_PD1360_INSTALLINST
- Sales Drawings - WDK_HBL2756_DRAWING_PDF
- Specifications - Wiring HBL2756 Specification Sheet
- Specifications - HBL2756 Specification Sheet French
- Specifications - HBL2756 Specification Sheet
- Warranty - Industrial & Commercial Products
- Video - Insulgrip Twist-Lock and Straight Blade Devices
- Video - Insulgrip Twist-Lock and Straight Blade Devices
- Video - Twist-Lock Devices



A Hubbell brand