

HUBBELL
Wiring Device-Kellems

By Hubbell Wiring Device-Kellems
Catalog # [HBL316P6W](#)

Heavy Duty IEC Pin and Sleeve Industrial Grade Male Plug, 16A
220-240V, 2-Pole 3-Wire Grounding, Terminal Screws,
Watertight



Features

-
-
-

Application

High Ampacity Connections

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - 3000V AC
- Electrical - Max. Working Voltage - 600V RMS
- Environmental - Flammability - HB or better per UL 94 or CSA C22.2 No. 0.17
- Environmental - Ingress Protection - IP67 Suitability
- Environmental - Moisture Resistance - Watertight per IEC 60309-1
- Environmental - Operating Temperatures - Maximum Continuous 75°C
- Minimum - 40°C w/o impact
- Mechanical - Impact Resistance - Per CSA C22.2 No.182.1 /UL1682
- Mechanical - Product Identification - Identification and ratings are a permanent part of the device housing
- Mechanical - Terminal Identification - Terminals identified in accordance with North American and IEC conventions

General

Catalog Number	HBL316P6W
EU RoHS Indicator	Yes
Environmental Conditions	Watertight
Item Type	Male Plug
Material	Composite
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
Series	HBL Heavy Duty
Specifications	<ul style="list-style-type: none">Cord Clamp - Reinforced Thermoplastic PolyesterHousing - Zytel® ST801 NylonLocking Ring - Reinforced Thermoplastic Polyester

	<ul style="list-style-type: none">Retainer - High-Impact ThermosetSealing Gasket - Solid Neoprene
Style	Standard Service
Type	Watertight Plug
UPC	783585403236

Dimensions

Display Size	Standard Sized
--------------	----------------

Electrical Ratings

Amperage Rating	16 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	16 A
Current Rating	16 A
Phase	Single Phase
Voltage Rating	220-240 VAC
Voltage Rating Description	220-240 VAC

Conductor Related

Cord Type	All Portable
Number Of Wires	3-Wire
Wire Size	#14 AWG to #10 AWG

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">CSA Certified File LR280CUL Classified to IEC 60309-1 IEC 60309-2UL Standard UL1682 and UL 1686C2
Nema Rating	Non-NEMA

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Engineering Drawing - HBL316P6W AutoCAD Drawing](#)
[Installation Manuals - WIRING_PD1303_INSTALLINST](#)
[Literature - PULP & PAPER SOLUTIONS](#)
[Literature - Pulp & Paper Solutions](#)

