

Straight Blade Devices, Isolated  
Ground, Receptacles, Duplex,  
Commercial/Industrial Grade, 2-  
Pole 3-Wire Grounding, 20A 125V,  
5-20R, Red, Single Pack

By Hubbell Wiring Device-Kellems  
Catalog # IG5362R



Straight Blade Devices, Isolated Ground, Receptacles, Duplex,  
Commercial/Industrial Grade, 2-Pole 3-Wire Grounding, 20A  
125V, 5-20R, Red, Single Pack

Features

- Triangle marking on face indicates isolated ground
- Slender compact design
- Finder Groove Face

Application

Extra Heavy Duty Specification Grade

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - Top: UL 94V-2, Base: UL 94V-0
- Environmental - Operating Temperatures - Maximum continuous 75°C, minimum -40°C (w/o impact)
- Mechanical - Product Identification - Ratings are a permanent part of the device
- Mechanical - Terminal Accommodation - #12-#10 AWG stranded or solid copper wire only
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

General

Catalog Number	IG5362R
Color	Red
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	1
Item Type	Traditional Duplex
Material	Nylon
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Series	Heavy Duty

Specifications

- Automatic Self-grounding Clip - Stainless steel
  - Base - PBT
  - Clamp - Nickel plated steel
  - Contacts - 0.031" (0.8) Brass
  - Face - Nylon
  - Mounting Screws - Zinc plated steel
  - Mounting Strap - .050 in. (1.3) Brass
  - Terminal Screws - Brass
- Finder Groove Face  
Standard Duplex  
783585876894

Style  
Type  
UPC

Dimensions

Dimensions	3.28 in x 1.33 in x 1.05 in
Display Size	Standard Sized Product
Height	1.05 in
Length	3.28 in
Weight	0.25 lb
Width	1.33 in

Electrical Ratings

Amperage Rating	20 A
Connectivity	Back and Side Wired Screw Terminals
Current / Amperage Rating	20 A
Current Rating	20 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	2500 W

Conductor Related

Number Of Wires	3-Wire
Wire Size	#12 AWG to #10 AWG

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"><li>• Certified to CSA, C22.2, No. 42 File 285</li><li>• Fed. Spec. WC596</li><li>• NEMA® WD-6 Compliant</li><li>• UL Listed to UL498 File No. E2186</li></ul>
Nema Rating	5-20R

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog Page - WDK A-10 Catalog Page](#)
- [Catalog Page - WDK M-17 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Installation Manuals - WIRING\\_PD2615\\_INSTALLINST](#)
- [Sales Drawings - WDK\\_IG5362R\\_DRAWINGS\\_PDF](#)
- [Specifications - Wiring IG5362R Specification Sheet](#)
- [Specifications - IG5362R Specification Sheet French](#)
- [Specifications - IG5362R Specification Sheet](#)
- [Warranty - Industrial & Commercial Products](#)



A Hubbell brand