



Straight Blade Devices, Receptacles, 4- Plex, Commercial/Industrial Grade, 2- Pole 3-Wire Grounding, 20A 125V, 5- 20R, Black, Single Pack

By Hubbell Wiring Device-Kellems
Catalog # [HBL420BK](#)



Straight Blade Receptacle, 4-Plex, Commercial/Industrial Grade, 2-Pole 3-Wire Grounding, 20A 125V, 5-20R.

Features

- Anchor hole and loop feature secures solid wire for fast, easy terminations
- Triple wipe contacts
- Easily accessible break-off tabs for split wiring
- Three conductors energize all four outlets

Application

Industrial

General

Color	<ul style="list-style-type: none"> • Black • Noir
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	1
Item Type	4-PLEX
Material	Polycarbonate
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	<ul style="list-style-type: none"> • Electrical: Current Interrupting: Capable of withstanding a fault level of 1000A, per UL498 • Dielectric Voltage: Withstands 2,000V minimum • Mechanical: Product Identification: Ratings are a permanent part of the device • Terminal Accommodation: #12 AWG stranded or solid copper conductor only • Terminal Identification: Terminals identified in accordance with UL 498 and CSA • Environmental:

Dimensions

Dimensions	4.30 in x 0.92 in x 4.30 in
Display Size	Standard Sized Product
Height	4.30 in
Length	4.30 in
Weight	0.4 lb
Width	0.92 in

Electrical Ratings

Amperage Rating	20 A
Connectivity	Screw Terminals
Current / Amperage Rating	20 A
Current Rating	20 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	2500 W

Conductor Related

Number Of Wires	3-Wire
Wire Size	#12 AWG

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • Certified to CSA 22.2, No. 42 File 285 • Listed to UL Standard 498 File E2186 • NEMA® WD-6 Compliant
Nema Rating	5-20R

Logistics

Carton Quantity	5
-----------------	---

Product Assets

[Catalog Page - WDK A-32 Catalog Page](#)
[Catalogs - WDK Catalog Full 2023](#)
[Engineering Drawing - HBL420BK AutoCAD Drawing](#)
[Installation Manuals - WIRING_D5510101_INSTALLINST](#)
[Sales Drawings - WDK_HBL420_DRAWING_PDF](#)
[Warranty - Industrial & Commercial Products](#)

Flammability: UL 94 V-2

- Operating Temperatures:
Maximum continuous 75°C
- minimum -40°C (w/o
impact)

Series
UPC

4-Outlet Receptacle
783585014524



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WDK_CA-HBL420BK-SPEC-EN | REV 1/2024