

Heavy Duty Products, Insulgrip Pin and Sleeve Devices, Industrial Grade, Back Box, For 60A and 100A 2" NPT Hub, Feed Thru, Mounting Screws Included

By Hubbell Wiring Device-Kellems
Catalog # [MB601008W](#)

Heavy Duty Products, Insulgrip Pin and Sleeve Devices, Industrial Grade, Accessories, Back Box, For 60A and 100A 2" NPT Hub, Feed Thru, Mounting Screws Included, Gray Cast Aluminum

Features

- Industrial Grade
- Back Box
- For 60A and 100A 2" NPT Hub

Application

Metallic

Performance

Electrical - Current Interrupting - Certified for current interrupting at full rated current, Electrical - Dielectric Voltage - Withstands 3,000V AC, Electrical - Max Working Voltage - 600V AC RMS, Environmental - Flammability - UL94-5VA and V-0 classification, Environmental - Operating Temperatures - Max. Continuous: 75° C, Min. Continuous: -40° C w/o impact, Mechanical - Impact Resistance - In accordance with UL746C, Mechanical - Product Identification - Identification and ratings are a part of the external label and molded into the receptacle mount, Mechanical - Terminal Identification - Terminals identified in accordance with North American and International conventions

Specifications

Standards - RoHS Compliance	CM
Status	
Industry Standard(s)	UL Listed
EU RoHS Indicator	Yes

Conductor

Cable Entry	Through Hub
-------------	-------------



Configuration

Knockouts	2" NPT Hub
Number Of Outlets	Accepts 1-Device

Dimensions

Display Size	For 60 and 100 Amp Devices
--------------	----------------------------

General

Specifications	• Assembly Screws - Stainless Steel • Box Hub Size - 2" NPT • Gaskets - Neoprene • Hinge Spring - Stainless Steel
Style	15 Degree
UPC	783585011349
Type	Four-Way Feed-Thru Back Box
Material - Mounting Hardware	Mounting Screws
Construction	Cast
Item Type	Mounting Box
Material	Aluminum
Series	Back Boxes and Adapters Series

Operational

Temperature Range	Limited By Device
-------------------	-------------------

Product Assets

- [Catalog \[English\]](#)
[Catalog Page \[English\]](#)
[Installation Manual \[French, English\]](#)