



Wiring Device-Kellems

Kellems Wire Management, Liquidtight System, PolyTuff® Non-Metallic Liquidtight Fittings, 90 Degree Male Liquid-Tight Connector, 1/2", Gray

By Hubbell Wiring Device-Kellems
Catalog # [PO509NGY](#)



PolyTuff® Non-Metallic 90° Liquidtight Fitting 1/2".

Features

- Nylon compression nut has a tapered dome to tighten ferrule onto conduit
- Neoprene O-ring provides liquidtight seal
- Non integral ferrule provides conduit seal and pullout protection

Application

Fittings are to be used with PolyTuff® I and PolyTuff® II

General

Color	<ul style="list-style-type: none"> • Gray • Gris
Material	Nylon
Performance	<ul style="list-style-type: none"> • Environmental - Flammability - UL 94X-2 • Environmental - Operating Temperature - -30°F to +225°F (-34°C to +107°C)
Style	90°
Type	<ul style="list-style-type: none"> • PolyTuff® Non-Metallic Liquidtight Fittings • PolyTuff® Non-Metallic Liquidtight Fittings
UPC	783585810010

Dimensions

Dimension - L Length Overall mm	2.91 in
Dimension - Thread Size	1/2" NPT
Height	1.98 in
Trade Size	1/2

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • CSA Certified • UL Listed:UL50 Type 4X, 12 and 13
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	25
-----------------	----

Product Assets

- [Catalog Page - WDK W-90 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2023](#)
- [Literature - Wire Management Solutions Brochure](#)
- [Literature - Safety Product Guide](#)
- [Literature - Industrial Solutions](#)
- [Sales Drawings - WDK_PO509N_DRAWING_PDF](#)
- [Warranty - Industrial & Commercial Products](#)
- [Video - Kellems Wire Management Solutions](#)

Related Products

- [G1050 - Kellems Wire Management, Liquidtight System, Non-Metallic PolyTuff® I Conduit, Gray, 1/2", 100 feet](#)
- [B2050 - Kellems Wire Management, Liquidtight System, PolyTuff® II Non-Metallic Tubing, 1/2", 100 feet, Black](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WDK_CA-PO509NGY-SPEC-EN | REV 1/2024