



Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female, Connector Body, 30A 3-Phase Delta 250V AC, Watertight

By Hubbell Wiring Device-Kellems
 Catalog # [HBL430C9W](#)



IEC Pin and Sleeve Watertight Female Connector 30A, 3-Phase 250V, 3-Pole 4-Wire.

Features

- Insulated Non-Metallic housing
- Color coded housings by voltage for easy identification
- Corrosion-resistant self-closing gasketed cover

Application

High Ampacity Connections

General

Color	<ul style="list-style-type: none"> • Blue • Bleu
Environmental Conditions	Watertight
Insulation	Insulated Body
Item Type	Standard
Material - Mounting Hardware	Cord Mounted
Number Of Poles	3-Pole
Performance	<ul style="list-style-type: none"> • Electrical - Current Interrupting - Certified for current interrupting at full rated current • Electrical - Dielectric Voltage - 3000V AC • Electrical - Max. Working Voltage - 600V RMS • Environmental - Flammability - HB or better per UL 94 or CSA C22.2 No. 0.17 • Environmental - Ingress Protection - IP67 Suitability • Environmental - Moisture Resistance - Watertight per IEC 60309-1 • Environmental - Operating Temperatures - Maximum Continuous 75°C • Minimum - 40°C w/o impact • Mechanical - Impact Resistance - Per CSA C22.2 No.182.1 /UL1682 • Mechanical - Product Identification -

Dimensions

Display Size Standard

Electrical Ratings

Amperage Rating	30 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	30 A
Current Rating	30 A
Voltage Rating	3 Phase 250 VAC
Voltage Rating Description	3 Phase 250 VAC

Conductor Related

Conductor Range	#12 AWG to #8 AWG
Number Of Conductors	4-Wire Grounding
Number Of Wires	4-Wire

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • CSA Certified File LR280C • UL Classified to IEC 60309-1 IEC 60309-2 • UL Listed, File E146033
----------------------	--

Nema Rating Non-NEMA

Logistics

Carton Quantity 10

Product Assets

- [Catalog Page - WDK G-10 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2023](#)
- [Engineering Drawing - HBL430C9W AutoCAD Drawing](#)
- [Installation Manuals - WIRING_PD1303_INSTALLINST](#)
- [Literature - IEC Pin & Sleeve Devices](#)
- [Literature - Safety Product Guide](#)
- [Literature - IEC Pin & Sleeve Devices](#)
- [Literature - Dual-Certified IEC Pin & Sleeve Devices](#)
- [Sales Drawings - WDK_HBL430C_DRAWING_PDF](#)
- [Warranty - Industrial & Commercial Products](#)

Identification
Identification and ratings
are a permanent part of
the device housing

- Mechanical - Terminal
Identification - Terminals
identified in accordance
with North American and
IEC conventions

Series	HBL Heavy Duty
Style	Standard Service
Temperature Rating	Maximum continu : 75° C ; Minimum continu : -40° C sans impact, -25° avec impact.
Type	<ul style="list-style-type: none">• Watertight Connector Body• Watertight Connector Body
UPC	783585404547



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WDK_CA-HBL430C9W-SPEC-EN | REV 1/2024