



Kellems Wire Management, Liquidtight System, PolyTuff® Straight Male Liquid Tight Connector, 1/2", Non-Metallic, Black

By Hubbell Wiring Device-Kellems
Catalog # [PO50NBKA](#)



PolyTuff® Non-Metallic Straight Liquidtight Fitting 1/2".

Features

- Nylon compression nut has a tapered dome to tighten ferrule onto conduit
- Neoprene O-ring provides liquidtight seal
- Non integral ferrule provides conduit seal and pullout protection

Application

Fittings are to be used with PolyTuff® I and PolyTuff® II

General

Color	<ul style="list-style-type: none">• Black• Noir
Material	Nylon
Performance	<ul style="list-style-type: none">• Environmental - Flammability - UL 94X-2• Environmental - Operating Temperature - -30°F to +225°F (-34°C to +107°C)
Style	Straight
Type	<ul style="list-style-type: none">• PolyTuff® Non-Metallic Liquidtight Fittings• PolyTuff® Non-Metallic Liquidtight Fittings
UPC	783585339122

Dimensions

Trade Size 1/2

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none">• CSA Certified• UL Listed:UL50 Type 4X, 12 and 13
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity 25

Product Assets

[Catalog Page - WDK W-90 Catalog Page](#)
[Catalogs - WDK Catalog Full 2023](#)
[Engineering Drawing - PO50NBKA AutoCAD Drawing](#)
[Installation Manuals - WIRING_PD1859_INSTALLINST](#)
[Literature - Wire Management Solutions Brochure](#)
[Literature - Safety Product Guide](#)
[Literature - Industrial Solutions](#)
[Literature - 50A Twist-Lock® Insulgrip® Conduit Adapters](#)
[Sales Drawings - WDK_PO50NBKA_DRAWING_PDF](#)
[Warranty - Industrial & Commercial Products](#)
[Video - Kellems Wire Management Solutions](#)

Related Products

[B2050 - Kellems Wire Management, Liquidtight System, PolyTuff® II Non-Metallic Tubing, 1/2", 100 feet, Black](#)
[G1050 - Kellems Wire Management, Liquidtight System, Non-Metallic PolyTuff® I Conduit, Gray, 1/2", 100 feet](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WDK_CA-PO50NBKA-SPEC-EN | REV 1/2024