



Locking Devices, Twist-Lock®, Valise, Female Connector Body, 15A 250V, 2-Pole 3-Wire Grounding, L6-15R, Screw Terminal, Black

By Hubbell Wiring Device-Kellems
Catalog # [HBL4579VBK](#)



Twist-Lock® Valise®, Female Connector Body, 15A 250V, 2-Pole 3-Wire Grounding, NEMA L6-15R, Screw Terminal Nylon.

Features

- Two captive multiple drive assembly screws
- Totally insulated impact and crush resistant nylon body
- Powerful cord grips prevent conductor slippage and strain on wiring terminals

Application

Heavy Duty Industrial

General

Color	Black
Cord Range	0.220"-0.660"(5.6-16.8)
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	15A Valise® Connector
Material	Nylon
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	<ul style="list-style-type: none"> • Electrical - Current Interrupting - Certified for full rated current • Electrical - Dielectric Voltage - Withstand 2,000V minimum • Environmental - Flammability - HB or better per UL 94 or CSA 22.2 No. 0.6 • Environmental - Moisture Resistance - IP20 Suitability • Environmental - Operating Temperatures - Maximum Continuous 75°C Minimum -40°C (w/o impact) • Environmental - Terminal Identification - Terminals identified in accordance with UL 498

Dimensions

Dimensions	1.50 in x 1.50 in x 2.59 in
Display Size	Standard
Height	2.59 in
Length	1.50 in
Weight	0.15 lb
Width	1.50 in

Electrical Ratings

Amperage Rating	15 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Voltage Rating	250 VAC
Voltage Rating Description	250 VAC

Conductor Related

Cable Range	0.220 - 0.660 in
Number Of Wires	3-Wire
Wire Size	#18 AWG to #12 AWG

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • Certified to CSA C22.2 No.42 • Fed.Spec. W-C-596 • Listed to UL 498
Nema Rating	L6-15R
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - WDK B-13 Catalog Page](#)
[Catalogs - WDK Catalog Full 2023](#)
[Installation Manuals - WIRING_PD1237_INSTALLINST](#)
[Sales Drawings - WDK_HBL4579VBK_DRAWING_PDF](#)
[Warranty - Industrial & Commercial Products](#)

Related Products

Related Products

- Mechanical - Terminal Accommodation - #18 AWG - #12 AWG stranded copper wire only.

[HBL4573VBK - Locking Devices, Twist-Lock®, Valise, Male Plug, 15A 250V, 2-Pole 3-Wire Grounding, L6-15P, Screw Terminal, Black and White](#)

[HBL4586C - Locking Devices, Twist-Lock®, Industrial, Flanged Inlet, 15A 250V, 2-Pole 3-Wire Grounding, L6-15P, Screw Terminal, White](#)

Temperature Rating

Maximum continu : 75° C ;
Minimum continu : -40° C sans impact, -25° avec impact.

Type

- Connector Body
- Connector Body

UPC

783585043227



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WDK_CA-HBL4579VBK-SPEC-EN | REV 1/2024