



# Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Female, Fused Mechanically Interlocked Receptacle, 60A 3-Phase Delta 250V AC

By Hubbell Wiring Device-Kellems  
Catalog # [HBL460MIF9W](#)



Heavy Duty IEC Pin and Sleeve Industrial Grade Female Fused Mechanically Interlocked Receptacle, 60A 3-Phase Delta 250V AC, 3-Pole 4-Wire Grounding, Terminal.

## Features

- Replaceable spring-loaded receptacle liftcover with gasket
- Removable door for ease of wiring and installation
- Plug-Check™ mechanism to detect the presence of plug

## Application

High Ampacity Connections

## General

Color	<ul style="list-style-type: none"> <li>• Blue</li> <li>• Bleu</li> </ul>
Environmental Conditions	Watertight
Item Type	Fused Mechanically Interlocked Single
Material	Thermoplastic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3-Pole
Performance	<ul style="list-style-type: none"> <li>• Electrical - Current Interrupting - Certified for current interrupting at full rated current and voltage</li> <li>• Electrical - Dielectric Voltage - Withstands 3,000V AC Min</li> <li>• Electrical - Max Working Voltage - 600V AC</li> <li>• Environmental - Flammability - UL94-5VA and V-0 Classification</li> <li>• Environmental - Ingress Protection - IP66 Suitability</li> <li>• Environmental - Operating Temperatures - Max. Continuous +75°C</li> <li>• Min. Continuous -40°C</li> <li>• Environmental - UV Resistance - All materials are UV stabilized</li> <li>• Mechanical - Impact Resistance - In accordance</li> </ul>

## Dimensions

Display Size Standard Sized Product

## Electrical Ratings

Amperage Rating	60 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	60 A
Current Rating	60 A
Phase	Three Phase
Voltage Rating	3 Phase 240 VAC
Voltage Rating Description	3 Phase 240 VAC
Wattage	15000

## Conductor Related

Number Of Wires	4-Wire
Wire Size	#8 AWG to #2 AWG

## Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> <li>• CSA Certified</li> <li>• UL Listed for US and Canada</li> </ul>
Nema Rating	Non-NEMA

## Product Assets

- [Catalog Page - WDK G-27 Catalog Page](#)
- [Catalog Page - WDK G-26 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2023](#)
- [Engineering Drawing - HBL460MIF9W AutoCAD Drawing](#)
- [Installation Manuals - WIRING\\_PD1781\\_INSTALLINST](#)
- [Literature - IEC Pin & Sleeve Devices](#)
- [Literature - Circuit-Lock® Motor Disconnects](#)
- [Literature - Improved Short Circuit Current Ratings \(SCCR\)](#)
- [Sales Drawings - WDK\\_HBL460MIF\\_DRAWING\\_PDF](#)
- [Warranty - Industrial & Commercial Products](#)

with UL 746C

- Mechanical - Mounting - External adjustment feet
- Mechanical - Terminal Identification - In accordance with UL, CSA and international conventions

Series

Fused

Style

Standard Service

Type

- Mechanical Interlock
- Mechanical Interlock

UPC

783585406039



**A proud member of the Hubbell Family.**

©2024 Hubbell Incorporated. All rights reserved.  
WDK\_CA-HBL460MIF9W-SPEC-EN | REV 1/2024