



# Locking Devices, Twist-Lock®, Industrial, Flush Receptacle, 15A 125V, 2-Pole 3-Wire Grounding, L5- 15R, Screw Terminal, Brown

By Hubbell Wiring Device-Kellems  
Catalog # [HBL4710](#)



Twist-Lock® Single Flush Receptacle, 15A 125V, 2-Pole, 3-Wire Grounding, NEMA L5-15R.

## Features

- Reinforced thermoplastic construction
- Single piece, all brass contacts
- All terminals are back and side wired
- Brass mounting strap with stainless steel grounding clip

## Application

Heavy Duty Industrial

## General

Color	<ul style="list-style-type: none"> <li>• Black</li> <li>• Noir</li> </ul>
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	0.5
Item Type	15A Single Flush Receptacle
Material	Nylon
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	<ul style="list-style-type: none"> <li>• Electrical - Current Interrupting - Certified for current interrupting at full rated current</li> <li>• Electrical - Dielectric Voltage - Withstands 2,000V minimum</li> <li>• Environmental - Flammability - HB or better per UL94/CSA 22.2 No.0.17</li> <li>• Environmental - Operating Temperatures - Maximum Continuous 75°C, Minimum -40°C (w/o impact)</li> <li>• Mechanical - Terminal Accommodation - #18 AWG - #10 AWG solid or stranded copper wire only.</li> <li>• Mechanical - Terminal Identification - Terminals identified in accordance with UL 498</li> </ul>

## Dimensions

Dimensions	3.28 in x 1.53 in x 1.27 in
Display Size	Standard Sized Product
Height	1.27 in
Length	3.28 in
Weight	0.20 lb
Width	1.53 in

## Electrical Ratings

Amperage Rating	15 A
Connectivity	Back and Side Wired
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V

## Conductor Related

Number Of Wires	3-Wire
Wire Size	#18 AWG to #10 AWG

## Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> <li>• Certified to CSA C22.2 No.42</li> <li>• Fed. Spec. W-C-596</li> <li>• Listed to UL 498</li> </ul>
----------------------	--

Nema Rating	L5-15R
Standards - RoHS Compliance Status	CM

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[BIM - Specialty\\_Equipment-Metal\\_Raceway-Hubbell\\_Wiring-Entrance\\_End\\_Fitting\\_Undivided-HBL4710](#)  
[Catalog Page - WDK N-18](#) [Catalog Page - WDK B-13](#) [Catalog Page - WDK O-33](#) [Catalog Page - WDK Catalog Full 2023](#)  
[Engineering Drawing - HBL4710 AutoCAD Drawing](#)  
[Installation Manuals - WIRING\\_PD2615\\_INSTALLINST](#)

Type

with UL 498

- Receptacle

- Receptacle

UPC

783585236728

Literature - Food Processing Guide  
Literature - Insulgrip® Straight Blade and Twist-Lock® Devices  
Literature - Healthcare Application Guide  
Literature - Industrial Solutions  
Literature - Education Application Guide  
Literature - Emergency Preparedness for Healthcare  
Literature - Entertainment Product Solution Guide  
Sales Drawings - WDK\_HBL4710\_DRAWING\_PDF  
Warranty - Industrial & Commercial Products  
Video - Insulgrip Twist-Lock and Straight Blade Devices  
Video - Twist-Lock Devices



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
WDK\_CA-HBL4710-SPEC-EN | REV 1/2024