

RMS121ILW

By Hubbell Wiring Device-Kellems  
Catalog # [RMS121ILW](#)

Trade Select, Switches and Lighting Controls, Vacancy Sensor Switch, With Night Light, 500W Max, 125V AC, White, Switch with Dimming

Application

No Buttons

General

Catalog Number	RMS121ILW
Control Output	Input Voltage
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Indicator(s) Type	PIR= Red LED
Item Type	Residential Wall Switches
Load Capacity	500W Incandescent @ 120V AC
Material - Mounting Hardware	Screw Mounting
Operating Cycles	6,000 Cycles Minimum
Operating Temperature	32 Deg F to 104 Deg F (0 Deg C to 40 Deg C)
Sensing Range	42 to 54 Inches above the Floor
Specifications	<ul style="list-style-type: none"><li>Product Type - Dimming Control Sensors</li></ul>



UPC

- Style - w/ Nightlight

883778301261

Electrical Ratings

Sensitivity	Adjustable W
Supply Voltage	120V AC V

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"><li>CEC Title 24 Certified</li><li>cULus Listed</li></ul>
----------------------	---

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalogs - WDK Catalog Full 2024](#)
- [Engineering Drawing - RMS121ILW AutoCAD Drawing](#)
- [Installation Manuals - WIRING\\_PD2203\\_INSTALLINST](#)
- [Sales Drawings - WDK\\_RMS121\\_DRAWING\\_PDF](#)
- [Specifications - RMS121ILW Specification Sheet English](#)
- [Specifications - RMS121ILW Specification Sheet French](#)